






LOC	DSRT	REVISIONS					
AI		P	LR	DESCRIPTION	DATE	DW	APP
		A1		REVISED PER ECR-17-014051	13OCT2017	BDA	KR




SEE DETAIL A



- MATES WITH APPROPRIATE UNIVERSAL MATE-N-LOK™ CAP OR HEADER.
 - SMALL NICKS ARE PERMITTED ON THE CIRCUIT TOWERS WHICH COULD INCREASE THE INITIAL HOUSING MATING FORCE BY UP TO 4.4 NEWTONS [1.0 LBS]. NO INDIVIDUAL NICKED TOWER SHALL INCREASE THIS FORCE BY OVER 2.2 NEWTONS [.5 LBS].
 - DIMENSIONS SHOWN REPRESENT PRODUCT IN DRY, AS MOLDED, CONDITION. ADDITIONAL 2% GROWTH DUE TO SUBSEQUENT MOISTURE ABSORPTION MAY OCCUR AND SHOULD BE ACCOUNTED FOR.
- △4 FOUR RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION. NO RIBS OR SIX RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION, OPTIONAL.
 - △5 NOT MANUFACTURED IN U.S.
 - △6 UNDERWRITERS RECOGNIZED COMPONENT LOGO AND CSA CERTIFICATION LOGO TO BE LOCATED ONCE ON EACH SIDE OF HOUSING.
 - △7 MATERIAL CORRESPONDING TO THE REQUIREMENTS OF IEC 60335 (INCL GLOW WIRE TEST 750°C WITHOUT FLAME)



DETAIL A
OPTIONAL CONSTRUCTION



3-DIMENSIONAL MODEL
NOT TO SCALE

MM	IN
33.02	1.300
27.43	1.080
20.32	.800
11.68	.460
0.38	.015
0.13	.005

CONVERSION TABLE

NATURAL	1863007-1
COLOR	PART NUMBER



THIS DRAWING IS A CONTROLLED DOCUMENT		DW	J. SALO	24JAN2008
		DR	J. LAZARO	24JAN2008
		APPD	L. BATLLO	24JAN2008
DIMENSIONS: mm		PROJECT SPEC	NME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	SIZE CASE CODE DRAWING NO	
0 P.L.C.	± .005	REQUIRE	A1 00779 ©=1863007	
1 P.L.C.	± .010	CUSTOMER DRAWING	SCALE 4:1 SHEET 1 OF 1 REV A1	
2 P.L.C.	± .013			
3 P.L.C.	± .015			
4 P.L.C.	± .020			
ANGLES	± # 0.20°			
FINISH	-			
MATERIAL	PA6			