


REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
	B	REVISED PER ECO-19-009164	23JUN2020	SJ DR



1. WIRE RANGE: 12-10 AWG. STANDARD WIRE CROSS SECTIONAL AREA RANGE: 5,180-13,100 CIRCULAR MILS, STRANDED
2. TERMINAL BODY MATERIAL THK IS  $0.990 \pm 0.076$  [ $.039 \pm .003$ ]
3. RECOMMENDED OPERATING TEMP  $-55^{\circ}\text{C}(-67^{\circ}\text{F})$  TO  $+200^{\circ}\text{C}(392^{\circ}\text{F})$  FOR HEAT SHRINK TUBING.
4. HEAT SHRINK TUBING SHELF LIFE OF 18 MONTHS FROM DATE CODE ON LABEL.

5.  $\triangle$  TERMINAL BODY PRODUCT SPECIFICATION 108-32046. APPLICATION SPECIFICATION 114-2162.

1	2-1197130-7	HIGH AND LOW TEMPERATURE CROSS LINKED FLUOROPOLYMER HEAT SHRINK TUBING 6.35 [.250] MIN ID X $25.40 \pm 2.03$ [ $1.000 \pm .080$ ], RT-555-1/4-0-SP
1	323064	TERMINAL BODY: COPPER PER ASTM B152 ANNEALED FINISH: NICKEL PLATE 0.00762 [.000300] MIN EXT THK PER SAE AMS QQ-N-290
-1	PART NO	DESCRIPTION

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 23AUG07	<b>STE</b> TE Connectivity	
DIMENSIONS: MM [ INCHES ]		CHK MJ SPICER 23AUG07		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD MJ SPICER 23AUG07	NAME HEAT RESISTANT TERMINAL KIT WIRE SIZE: 12-10 AWG	
0 PLC $\pm -$		PRODUCT SPEC $\triangle 5$	SIZE	
1 PLC $\pm -$		APPLICATION SPEC $\triangle 5$	CAGE CODE	
2 PLC $\pm -$			DRAWING NO	
3 PLC $\pm 0.127$ [.005]			RESTRICTED TO	
4 PLC $\pm -$			A300779 C-1958126	
ANGLES $\pm 1^{\circ}$			SCALE 1:1	
MATERIAL SEE TABLE		FINISH SEE TABLE	SHEET 1 OF 1	
		WEIGHT -	REV B	
		CUSTOMER DRAWING		