







REVISIONS					
REV	DESCRIPTION	DATE	BY	APP'D	REV
B1	MODIFIED AS PER ECR-23-169440	31MAR2023	KV	HW	



- MATERIAL:  
HOUSING - PCT POLYESTER, BLACK, UL94V-0.  
OVERMOLDED TERMINAL ARRAY - HIGH TEMPERATURE NYLON, COLOR: NATURAL  
TERMINALS - 0.33 [.013] THICK PHOS BRONZE PLATED WITH 1.27um [.000050] MIN THICK HARD GOLD IN LOCALIZED AREA AND 3.81um [.000150] MIN THICK MATTE TIN IN SOLDER AREA OVER 1.27um [.000050] MIN THICK NICKEL UNDERPLATE.  
OUTER SHIELD AND INNER SHIELD-0.25[.010] THICK COPPER ALLOY PLATED WITH 1.27um[.000050] MIN NICKEL. PCB GROUND TABS DIPPED WITH 2.03um[.000080] MIN TIN
- JACK CAVITY CONFORMS TO FCC RULES AND REGULATIONS, PART 68 SUBPART F.
- DATE CODE LOCATED ON REAR OF PART APPROXIMATELY AS SHOWN:  
FIRST 2 DIGITS ARE LAST 2 DIGITS OF YEAR, SECOND 2 DIGITS ARE MANUFACTURING WORK WEEK, LAST DIGIT IS DAY OF WEEK, WITH SUNDAY = 1.
- PARTS PACKAGED IN SEALED BAGS WITH DESICCANT
- PARTS SUITABLE FOR LEAD FREE REFLOW PROCESSING TO 260° C



PC BOARD LAYOUT VIEWED FROM COMPONENT SIDE SCALE 2:1

2007105-1  
PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN T. SPRINKLE/12SEPT2007		APPROVED J. WESTMAN/12SEPT2007	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME S. FLICKINGER/12SEPT2007	
0 PLC	±	0.25[.01]	1 PLC	±	0.13[.005]
1 PLC	±	0.13[.005]	2 PLC	±	0.08[.003]
2 PLC	±	0.08[.003]	3 PLC	±	0.05[.002]
3 PLC	±	0.05[.002]	4 PLC	±	0.03[.001]
4 PLC	±	0.03[.001]	ANGLES	±	±
MATERIAL SEE NOTE 1	FINISH SEE NOTE 1	WEIGHT 0.000000	SIZE 114-2048	CAGE CODE 00779	DRAWING NO. C=2007105
CUSTOMER DRAWING		SCALE 4:1	SHEET 1 of 1	REV B1	