

4

3

2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - TE Connectivity ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	K	REVISED PER ECO-20-001083	30JAN2020	SM	MZ
	G1	REVISED PER ECO-09-021826	12JAN10	KK	AEG
	H	REVISED PER ECO-17-011181	03AUG2017	RS	MZ
	J	REVISED PER ECO-18-000443	30JAN2018	RS	MZ

Dimensions and Tolerances:

- Overall height: 48.26 ± 0.38 [1.900 ± .015]
- Top section height: 23.88 ± 0.38 [.940 ± .015] TYP
- Side view height: 41.91 [1.650] TYP
- Pin diameter: $\phi 3.23 \pm 0.08$ [$\phi .127 \pm .003$] 4 PLC
- Pin length: 7.75 [.305] TYP
- Pin offset: 5.08 [.200] TYP
- Pin diameter: $\phi 1.02 \pm 0.05$ [$\phi .040 \pm .002$] 6 PLC
- Pin length: 13.97 ± 0.38 [.550 ± .015] TYP
- Pin offset: 8.25 [.325]
- Pin length: ± 0.51 [$\pm .020$] 6 PLC

1 HOUSING MATERIAL: PA66, BLACK, UL 94 V-0 RATED.
 2 BRASS PER ASTM B36.
 3 $3.81 \mu\text{m}$ [.000150] MIN TIN-LEAD OVER $2.54 \mu\text{m}$ [.000100] MIN COPPER.
 4 $3.81 \mu\text{m}$ [.000150] MIN TIN OVER $2.54 \mu\text{m}$ [.000100] MIN COPPER.
 5 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

5	OBSOLETE	4	12.83 [.505]	-208116-5-
		4	3.05 [.120]	208116-4
	OBSOLETE	3	12.83 [.505]	208116-3
	OBSOLETE	3	3.05 [.120]	208116-1
		CONTACT FINISH	L	PART NUMBER

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN		CHK		APVD		NAME	
mm	[INCHES]										
		0 PLC	± -	J. MCCLINTON	11/06/91						
		1 PLC	± -	R. STONE	11-8-91						
		2 PLC	± 0.25 [.010]	TE Connectivity HEADER ASSEMBLY, PIN, 6 POSITION, METRIMATE							
		3 PLC	± -	SIZE CAGE CODE DRAWING NO RESTRICTED TO A2 00779 C-208116							
		4 PLC	± -	WEIGHT - SCALE 2:1 SHEET 1 OF 1 REV K							
		ANGLES	± -	CUSTOMER DRAWING							
MATERIAL		FINISH		CONTACTS: SEE TABLE							
HOUSING: 1											
CONTACTS: 2											

1471-9 (1/15)

208116

A