




REVISIONS				
P	LTN	DESCRIPTION	DATE	OWN APVD
B1		REVISED PER ECO-14-018036	17FEB2015	AP DD
B2		REVISED PER ECN-24-252171	23FEB2024	AP RS



⚠ MATERIAL:
 HOUSING: LCP, GLASS FILLED, UL94V-0.
 TERMINALS: HIGH PERFORMANCE COPPER ALLOY.



⚠ FINISH:
 30µ" SELECTIVE GOLD IN CONTACT AREA. SELECTIVE TIN ON PCB TAILS, NICKEL OVERALL.

3. CONNECTORS SUPPLIED WITH MOUNTING SCREWS.



SCALE 4:1

REFER TO WWW.TE.COM FOR PRODUCT AVAILABILITY



KEY POSITION CHART	
	NONE
	A
	B
	C
	D
	E
	F
	G
	H

144X $\varnothing 0.39 \pm 0.05$ PLATED THRU HOLE
 144X $\varnothing 0.46 \pm 0.013$ DRILL HOLE
 $\varnothing 0.10$

OFFSET BETWEEN BOARD AND BACKPLANE HOLE COLUMNS

RECOMMENDED PCB LAYOUT
 MIN BOARD THICKNESS 1.0

KEY POSITION	FINISH	PART NUMBER
H	⚠	8-2057960-1
G	⚠	7-2057960-1
F	⚠	6-2057960-1
E	⚠	5-2057960-1
D	⚠	4-2057960-1
B	⚠	2-2057960-1
A	⚠	1-2057960-1
NONE	⚠	2057960-1

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		MATERIAL:	
mm	0 PLC	±	0.2	SEE TABLE	SEE TABLE
	2 PLC	±	0.13		
	3 PLC	±	0.1		
	4 PLC	±	0.075		
	ANGLES	±	0.5		

STE TE Connectivity

IMPACT, 4 PAIR, DAUGHTERCARD
 12 COLUMN, RIGHT GUIDED, SIGNAL
 MODULE, 0.39 EYELET

SIZE: CAGE CODE DRAWING NO. RESTRICTED TO
 A100779C=2057960

CUSTOMER DRAWING SCALE 6:1 SHEET 1 OF 1 REV B2