





LOC		DIST		REVISIONS			
GP	00	P	LTN	DESCRIPTION	DATE	DWN	APVD
		A		REVISED PER ECO-15-000199	13JAN2015	AP	DG
		C		REVISED PER ECO-18-008478	10MAY2018	JY	SH

- 1 MATERIALS  
 HOUSINGS AND CHICKLETS: LCP, BLACK, UL94V-0 RATED  
 CONTACTS: COPPER ALLOY
- 2 CONTACT FINISH: CONFORMS TO THE REQUIREMENTS OF TE PRODUCT SPECIFICATION, 108-32038. BASED ON EIA/ECA-364-1000.01A. (CONTROLLED ENVIRONMENT APPLICATIONS) ON MATING END. TIN PLATED ON PCB TAIL
- 3. MATES WITH TE PLUG 2227603-1
- 4 MOUNTING HARDWARE M2x1.35 SELF-THREADING SCREW  
 SCREW LENGTH OF FASTENER = PCB THICKNESS + 3.0mm MAX (1.75mm MIN)  
 MOUNTING HARDWARE IS NOT SUPPLIED BY TE.
- 5 RECOMMENDED COMPONENT KEEP OUT ZONE.
- 6 PART NUMBER AND DATE CODE MARKED IN APPROXIMATE AREA SHOWN ON OPPOSITE SIDE.
- 7 MOUNTING HARDWARE M2x0.0.78 OR M1.8x0.709 SELF-THREADING SCREW (DELTA PT® THREAD-FORMING FASTENER), SCREW LENGTH OF FASTENER = PCB THICKNESS + 5.0mm MAX (1.75mm MIN), MOUNTING HARDWARE IS NOT SUPPLIED BY TE.




SCALE 4:1


7	Ø1.60	2227582-2
4	Ø1.80	2227582-1
SCREW APPLICATION	DIAMETER OF SCREW HOLES	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: R. IREA 20DEC2012	TE Connectivity	
DIMENSIONS: mm		CHK: R. HENRY 20DEC2012	RECEPTACLE ASSEMBLY, 1X4, RIGHT ANGLE, INTERNAL MINI-SAS HD	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD: -	NAME	
0 PLC	±	PRODUCT SPEC	108-32038	
1 PLC	±0.13	APPLICATION SPEC	114-32101	
2 PLC	±	WEIGHT	A100779C=2227582	
3 PLC	±	CUSTOMER DRAWING	SCALE 6:1	SHEET 1 OF 3
4 PLC	±			REV C
ANGLES	±			
FINISH	±			

LOC	DIST	REVISIONS			
P	LTN	DESCRIPTION	DATE	DWN	APVD
GP	00	- SEE SHEET 1	-	-	-





2227582-1  
SCALE 6:1



2227582-2  
SCALE 6:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. IREA 20DEC2012	TE Connectivity
DIMENSIONS: mm		CHK R. HENRY 20DEC2012	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0.13 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH		APVD -	NAME RECEPTACLE ASSEMBLY, 1X4, RIGHT ANGLE, INTERNAL MINI-SAS HD
MATERIAL		PRODUCT SPEC 108-32038	RESTRICTED TO
		APPLICATION SPEC 114-32101	SIZE CAGE CODE DRAWING NO A100779C=2227582
		WEIGHT	SCALE 6:1 SHEET 2 OF 3 REV C
		CUSTOMER DRAWING	

LOC	DIST	REVISIONS			
P	LTN	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



RECOMMENDED PCB LAYOUT  
SCALE 6:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. TREA	Z0DEC2012	TE Connectivity
DIMENSIONS:		CHK R. HENRY	Z0DEC2012	
mm	0 PLC ±	APVD		NAME
	1 PLC ±	PRODUCT SPEC		RECEPTACLE ASSEMBLY, 1X4, RIGHT ANGLE, INTERNAL MINI-SAS HD
	2 PLC ±0.13	APPLICATION SPEC		SIZE
	3 PLC ±	WEIGHT		A100779C=2227582
	4 PLC ±	FINISH		RESTRICTED TO
MATERIAL	ANGLES	CUSTOMER DRAWING		SCALE 6:1 SHEET 3 OF 3 REV C