





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
A1		REVISED PER ECR-23-173068	13DEC2023	P.C	D.Z




- 1 WIRE RANGE 0.13-0.3mm² [26-22 AWG]
- 2 INSULATION RANGE 1.20-1.75
- △3 FINISH: 1.27µm MIN NICKEL ALL OVER
- △4 FINISH: 0.76µm MIN GOLD ON INNER SURFACE, PERMITTED ON OUTER SURFACE.
- △5 FINISH: 2.54µm MIN TIN ON ALL SURFACES IN THIS AREA.
- △6 FINISH: 2.54µm MINIMUM PRE-TIN OVERALL
- △7 PRELIMINARY PART - NOT RELEASED FOR PRODUCTION
THIS PRODUCT HAS NOT COMPLETED QUALIFICATION TESTING



SECTION A-A



SECTION B-B



SECTION C-C

△5 GOLD △3 △4	PHOS BRONZE	△7 2238018-4
PRE-TIN △6	PHOS BRONZE	△7 2238018-3
△5 GOLD △3 △4	BRASS	△7 2238018-2
PRE-TIN △6	BRASS	2238018-1
FINISH	MATERIAL	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 10MAY2013	TE TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK K RANDOLPH 09MAY13		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD K RANDOLPH 09MAY13	NAME PIN TERMINAL, VAL-U-LOK	
0 PLC ± - 1 PLC ± 0.3 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC 108-2112	SIZE A2	
MATERIAL SEE TABLE		APPLICATION SPEC 114-13172	CAGE CODE 00779	DRAWING NO C=2238018
FINISH SEE TABLE		WEIGHT -	SCALE 8:1	SHEET 1 OF 1
CUSTOMER DRAWING			RESTRICTED TO -	REV A1