



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - TE Connectivity Ltd. ALL RIGHTS RESERVED.

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
	B1	REVISED PER ECR-16-004169	19JAN2020	RZ RS



- 1 ZINC PER QQ-Z-363.
- 2 BERYLLIUM COPPER PER ASTM-B-643
- 3 PTFE PER MIL-P-19468.
- 4 COPPER-IRON ALLOY PER ASTM-B-465.
- 5 COPPER PER QQ-C-576.
- 6 COPPER ALLOY PER ASTM-B-122.
- 7 NICKEL PLATE PER QQ-N-290
3.81µm [.000150] MINIMUM THICK.
- 8 GOLD PLATE PER MIL-G-45204
0.20µm [.000008] MINIMUM THICK.
- 9 TIN PLATE PER ASTM-B-545,
2.54 µm [.000100] MIN THICK.
- 10 GOLD PLATE PER MIL-G-45204
- 11 CONNECTOR PRESS FIT IS DESIGNED TO PROVIDE 100 LB. MINIMUM AXIAL RETENTION TO PCB COMPLIANT WITH TYCO APPLICATION SPEC 114-12001. AS A RESULT, DEFORMATION OF PLATED THROUGH HOLES WILL OCCUR. CUSTOMER VALIDATION AND ACCEPTANCE OF THIS DEFORMATION IS RECOMMENDED PRIOR TO SPECIFYING USE OF THIS PRODUCT.



PCB CONFIGURATION

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. ALCORTA - DOCK5 21APR2005	TE Connectivity	
		CHK J. HAVENER 21APR2005		
DIMENSIONS: mm [INCHES]		APVD J. LIPPERT 21APR2005	NAME JACK, PCB, HIGH RETENTION PRESS FIT, 50 OHM, BNC	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC 108-12103	RESTRICTED TO	
0 PLC ± -		APPLICATION SPEC 114-12001	SIZE A2	CAGE CODE 00779
1 PLC ± -		WEIGHT 0.000000	DRAWING NO C-5222006	REV B1
2 PLC ± 0.05 [.002]		CUSTOMER DRAWING		
3 PLC ± -		SCALE 5:1	SHEET 1 of 1	
4 PLC ± -				
ANGLES ± -				
FINISH				
SEE NOTES 1-6				
SEE NOTES 7-10				