





REVISIONS					
P	LTR	DESCRIPTION	DATE	DMN	APVD
A		REVISED PER ECO-20-013368	28SEP2020	RZ	HL



- △ HOUSING MATERIAL: LIQUID CRYSTAL POLYMER.
COLOR: NATURAL.
- △ CONTACT MATERIAL: PHOSPHOR BRONZE.
- △ CONTACT FINISH:(B)
UNDERPLATE (ENTIRE CONTACT):
0.00127 MIN NICKEL PER SAE-AMS-QQ-N-290
ON MATING SURFACES:
CONFORMS TO ALL TESTING SPECIFIED FOR TELCORDIA
UNCONTROLLED ENVIRONMENT.
ON LEADS:
0.0006 MIN MATTE TIN PER ASTM B 545 OVER UNDERPLATE.
LUBRICATION (MIN MATING SURFACES):
SURFACE CONDITIONER AFTER PLATING.
- △ PART MARKING, LOCATED APPROXIMATELY AS SHOWN.
- △ DIMENSION APPLIES WHEN SEATED ON PRINTED CIRCUIT BOARD.
- △ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI




RECOMMENDED CIRCUIT PATTERN
(COMPONENT SIDE)

N	7.25	4.25
J	6.50	4.25
A	5.00	4.25
CONTACT LETTER	DIM Y	DIM Z

E	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	E
D	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	D
C	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	C
B	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	B
A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A
ROW 1																		

CONTACT LOAD CHART



OBSOLETE	48	94.00	47	95.88	240	5223058-8
	36	70.00	35	71.88	180	5223058-6
	24	46.00	23	47.88	120	5223058-4
△ OBSOLETE	18	34.00	17	35.88	90	5223058-3
	12	22.00	11	23.88	60	5223058-2
	X					
	NUMBER OF COLUMNS	DIM C	B	DIM A	NUMBER OF SIGNAL POSITIONS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN B MCMMASTER 24NOV04	TE Connectivity
DIMENSIONS: mm		CJK R WERTZ 24NOV04	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	PIN ASSEMBLY, Z-PACK 2mm FB, SIGNAL, VERTICAL, 5 ROW, WITH PRESS FIT LEADS
0 PLC ± -		APPLICATION SPEC	
1 PLC ± 0.13		WEIGHT	SIZE CASE CODE DRAWING NO RESTRICTED TO
2 PLC ± -		A1 00779 C=5223058	SCALE 4:1 SHEET 1 OF 2 REV A
3 PLC ± -		CUSTOMER DRAWING	
4 PLC ± -			
ANGLES ± -			

REVISIONS				
#	LR	DESCRIPTION	DATE	APVD
-	-	SEE SHEET 1	-	-

N	7.25	4.25
J	6.50	4.25
A	5.00	4.25
CONTACT LETTER	DIM Y	DIM Z

E	A	A	A	A	A	A	A	A	A	A	A	A	E	5223058-2
D	J	J	J	J	J	J	J	J	J	J	J	J	D	
C	N	N	N	N	N	N	N	N	N	N	N	N	C	
B	J	J	J	J	J	J	J	J	J	J	J	J	B	
A	A	A	A	A	A	A	A	A	A	A	A	A	A	
ROW	1	2	3	4	5	6	7	8	9	10	11	12	ROW	PART NUMBER

CONTACT LOAD CHART

E	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	E	5223058-3			
D	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	D				
C	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	C				
B	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	B				
A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A				
ROW	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	ROW	PART NUMBER

CONTACT LOAD CHART

E	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	E	5223058-4					
D	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	D						
C	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	C						
B	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	B						
A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A						
ROW	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	ROW	PART NUMBER

CONTACT LOAD CHART

E	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	E	5223058-6	
D	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	D		
C	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	C		
B	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J		B
A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A		A
ROW	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36	ROW	PART NUMBER

CONTACT LOAD CHART

E	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	E	5223058-8											
D	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	D												
C	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	C												
B	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J	J		B										
A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A	A												
ROW	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36	37	38	39	40	41	42	43	44	45	46	47	48	ROW	PART NUMBER

CONTACT LOAD CHART

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG: B.MCMMASTER 24NOV04	TE Connectivity
DIMENSIONS: mm		CHK: R.WERTZ 24NOV04	
		TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME: R.WERTZ 24NOV04
0 PLC ± - 1 PLC ± - 2 PLC ± 0.13 3 PLC ± - 4 PLC ± - ANGLES ± -		APVD: R.WERTZ 24NOV04	PRODUCT SPEC: -
MATERIAL: FINISH: -		APPLICATION SPEC: -	RESTRICTED TO: -
WEIGHT: -		SIZE: A1	CAGE CODE: 00779
CUSTOMER DRAWING		DRAWING NO: 5223058	SCALE: 4:1
		SHEET: 2	OF: 2
		REV: A	