

SPECIFICATION CONTROL DRAWING

55PC0822

TITLE

TWO CONDUCTOR CABLE, UNSHIELDED, UNJACKETED, 600 VOLT

Date


11-03-00

Revision

B

This specification sheet forms a part of the latest issue of Raychem Specification 55PC.

COMPONENT WIRES - 55PC0812



CONSTRUCTION DETAILS

PART NUMBER	CONDUCTOR SIZE (AWG)	DIAMETER (in.)			WEIGHT (lb/1000 ft.)	
		LOWER SPEC LIMIT	TARGET VALUE	UPPER SPEC LIMIT	TARGET VALUE	UPPER SPEC LIMIT
55PC0822-24-*	24	.084	.087	.090	4.41	4.66
55PC0822-22-*	22	.096	.099	.102	6.31	6.60
55PC0822-20-*	20	.113	.116	.119	9.39	9.72
55PC0822-18-*	18	.132	.136	.139	14.05	14.57
55PC0822-16-*	16	.148	.152	.156	17.81	18.40
55PC0822-14-*	14	.180	.184	.188	27.32	28.09
55PC0822-12-*	12	.216	.221	.226	41.39	42.38
55PC0822-10-*	10	.260	.266	.272	64.23	65.86
55PC0822-8-*	8	.384	.392	.400	116.	119.

CABLE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 200°C
 Maximum continuous conductor temperature
 VOLTAGE RATING: 600 volts (rms)

INSULATION FLAWS:
 Impulse Dielectric Test, 8.0 kV (peak)

PART NUMBER:
 The "*" in the part numbers above shall be replaced by a color code designator with a slash separating the component wire colors.
 Example: AWG 22, black and white component wires;
 55PC0822-22-0/9

COLOR AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681.

THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HEREIN.
 REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID.

Raychem

300 Constitution Drive
 Menlo Park, California 94025
 1-800-2 Raychem FAX: 1-650-361-6