


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	26NOV2012	WI	WI
	B	ECN-22-137020	31JAN2022	LS	GS
	B1	ECR-22-153829	27SEP2022	CAK	CAK
	B2	REVISED PER ECR-23-174746	09MAY2023	SS	MA

HAND TOOL SOLARLOK PV4 PIN AND SOCKET CONTACTS



CSV10 VARIO LONG HANDLES TCPN 2-1579005-2

CRIMP HEAD TCPN 4-1579016-7
WITH CONTACT LOCATOR

CONTACT LOCATOR TCPN 7-1579025-3
AS SPARE PART AVAILABLE

CONTACT	WIRE SIZE MM ² /AWG	WIRE CRIMP		STRIPP LENGTH MM	INSTRUCTION SHEET
		HEIGHT MM	WIDTH MM		
2270100 (SOCKET) 2270099 (PIN) 2270253 (SOCKET) 2270252 (PIN) 2368158 (SOCKET) 2368157 (PIN)	4.0/AWG12	2.14±0.05	3.94	6.5 ⁺¹ _{-0.05}	411-18554
2270100 (SOCKET) 2270099 (PIN) 2270253 (SOCKET) 2270252 (PIN) 2368158 (SOCKET) 2368157 (PIN)	6.0/AWG12	2.49±0.05	3.94	6.5 ⁺¹ _{-0.05}	411-18554

1. PROCESSING OF TERMINALS ACCORDING TO APPLICATION SPECIFICATION 114-106078.
2. DIMENSION: 250x65x60MM (LxWxH).

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ±-
	1 PLC ±-
	2 PLC ±-
	3 PLC ±-
	4 PLC ±-
	ANGLES ±1°
MATERIAL	FINISH
-	-

DWN	C. WITT	26NOV2012
CHK	C. Witt	26NOV2012
APVD	C. WITT	26NOV2012
PRODUCT SPEC	-	-
APPLICATION SPEC	-	-
WEIGHT	470g	-
CUSTOMER DRAWING	-	-



NAME HAND TOOL SOLARLOK PV4			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	6-1579014-8	-
SCALE	SHEET	OF	REV
-	1	1	B2