


- 1 HOUSING MATERIAL: GLASS-FILLED POLYMER.
- 2 POST MATERIAL: COPPER ALLOY.
- 3 POST FINISH: DIN 41612 CLASS 2 IN CONTACT AREA. TIN PLATE ON POSTS.
- 4 PART NUMBER, DATE CODE MARKED THIS APPROXIMATE AREA.
- 5 MARKING ON THIS SIDE.
- 6 RECOMMENDED HOLE SIZE FOR MANUAL APPLICATION OF CONNECTOR ONTO PC BOARD.
- 7 CONTACT AREA FINISH: 0.00076 [.000030] MIN GOLD OVER 0.00127 [.000050] MIN NICKEL. TAIL FINISH: 0.0025 [.000100] MIN MATTE TIN OVER 0.00127 [.000050] MIN NICKEL.
- 8 CONTACT AREA FINISH: 0.00127 [.000050] MIN GOLD OVER 0.00127 [.000050] MIN NICKEL. TAIL FINISH: 0.0025 [.000100] MIN MATTE TIN OVER 0.00127 [.000050] MIN NICKEL.



SECTION Z-Z

REFERENCE FAMILY DRAWING 650473 FOR ALL TYPE C HEADER OFFERINGS

SUPERSEDED BY 5650473-5	1-32	X	X	X	-	7	96	7-5650473-5
	1-32	X	X	X	7	7	96	5650473-6
	1-32	X	X	X	3	7	96	5650473-5
	1-32	X	X	X	8	7	96	5650473-1
	POSITIONS LOADED	C	B	A				
	ROWS LOADED							
					FINISH		NO. OF LOADED POSITIONS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN J. POLIGNONE DSMAYOS		TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD A. SHARPE DSMAYOS NAME	
0 PLC	± -	0 PLC	± -	ASSEMBLY, PIN EUROCARD, TYPE C, 96 POSITION, .104 SOLDER POST	
1 PLC	± -	1 PLC	± 0.13[.005]	SIZE CAGE CODE DRAWING NO RESTRICTED TO	
2 PLC	± -	2 PLC	± -	WEIGHT	
3 PLC	± -	3 PLC	± -	A1 00779 C=5650473	
4 PLC	± -	4 PLC	± -	CUSTOMER DRAWING SCALE 5:1 SHEET 1 OF 1 REV C	
ANGLES	± -				