


## CUSTOMER DRAWING



Product Name	Product Dimensions				Cable Dimensions				
	L max	A min	B min	K min	D max	E min	F min	J±1 (J±0.04)	G max
B-014-105-01	37.5 (1.470)	9 (0.355)	11 (0.430)	200 (7.900)	10.8 (0.425)	4.6 (0.180)	4.4 (0.175)	13 (0.510)	8.8 (0.350)


### MATERIAL

- INSULATION SLEEVE: Heat-shrinkable, radiation cross-linked modified polyolefin. Transparent clear.
- SOLDER PREFORM WITH FLUX:  
SOLDER: TYPE Cd18 per ANSI J-STD-006.  
FLUX: TYPE ROM1 per ANSI J-STD-004.
- & 4. INSULATION SLEEVES: Heat-shrinkable, radiation cross-linked modified polyolefin.
- GROUND LEAD: RAYCHEM 55A0111-18 in accordance with MIL-W-22759/32 AWG 18 stranded tin plated copper wire.  
Color: white.

### APPLICATION

- These parts are designed to provide an environment protected shield termination on cables, rated for 85°C minimum. meeting the dimensional criteria listed. Having bare copper or tin plated shields.
- Temperature range: -55°C to +125°C.
- Install using TE Connectivity-approved convection or infrared tools in accordance with Raychem installation procedure RPIP-709-00.

For best results, prepare the cable as shown:



TE Connectivity, TE connectivity (logo), Raychem, Thermofit, and SolderSleeve are trademarks

		<b>Raychem THERMOFIT DEVICES</b>		TITLE: <b>SOLDERSLEEVE DEVICE WITH PRE-INSTALLED LEAD LOW TEMPERATURE</b>	
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. INCHES DIMENSIONS ARE IN BETWEEN BRACKETS.				DOCUMENT NO: B-014-105-01	
TOLERANCES: 0.00 N/A 0.0 N/A 0 N/A	ANGLES: N/A  ROUGHNESS IN MICRON	TE Connectivity reserves the right to amend this drawing at any time. Users should evaluate the suitability of the product for their application.		Revision: <b>A</b>	Issue Date: <b>April 2020</b>
DRAWN BY: <b>R. MAPALO</b>		DATE: <b>07/06/98</b>	ECO: ECO-20-004959		SCALE: <b>NONE</b>
				SIZE: <b>A</b>	SHEET: <b>1 of 1</b>