



REVISIONS				
變更				
P	LTR	DESCRIPTION	DATE	DWN APVD
B		OBSOLETE (ECO-20-016729)	02MAR2021	A.L H.L

AS SHOWN: TYPE-1




D-D (SCALE 2:1)




△ TRAY TYPE-1 AND TYPE-2 MUST BE PILED UP BY TURNS. (REFER TO PACKING SPECIFICATIONS)



E-E (SCALE 2:1)



OBSOLETE



DETAIL C (SCALE 1:1)

SEALANT	TOOLING STATUS	ROW	QTY	B	A	POS.	TRAY P/N	PART NO.
NOT AVAILABLE					48.7	280	5- -3	6- -0
NOT AVAILABLE					42.7	240	5- -2	5- -9
NOT AVAILABLE		3	18	70	36.7	200	5- -1	5- -8
NOT AVAILABLE		3	18	70	54.7	320	5- -4	1- -1
NOT AVAILABLE					48.7	280	5- -3	1- -0
NOT AVAILABLE					42.7	240	5- -2	-9
NOT AVAILABLE		3	18	70	36.7	200	5-912069-1	6318157-8

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN HAWKING HE 13DEC04
 CHK STEVEN YAO 13DEC04
 APVD I. ENOMOTO 13DEC04 NAME 名称


PRODUCT SPEC 108-60047
 APPLICATION SPEC 114-5255
 WEIGHT

TE Connectivity Ltd.
 SOFT TRAY ASSY
 FH 0.6BTB CONNECTOR
 REC 4H W/G-CONT 2ROW TYPE

SIZE A3 CAGE CODE 00779 DRAWING NO. G=6318157 RESTRICTED TO


CUSTOMER DRAWING SCALE 1:2 SHEET 1 OF 6 REV B

GENERAL TOLERANCE 一般公差
 10 ≥ ±0.2
 30 ≥ >10: ±0.25
 100 ≥ >30: ±0.3
 ANGLES: ±3°



TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差
 0 PLC ± -
 1 PLC ± -
 2 PLC ± -
 3 PLC ± -
 4 PLC ± -
 ANGLES ± -
 FINISH 仕上


REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
-	-	SEE SHEET 1	-	-




REFERENCE P.C.BOARD LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	TE Connectivity Ltd.		
DIMENSIONS: 单位: 耗 mm		CHK			
TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差		APVD	NAME 名称 SOFT TRAY ASSY FH 0.6BTB CONNECTOR REC 4H W/G-CONT 2ROW TYPE		
GENERAL TOLERANCE 一般公差 10≥:±0.2 30≥ >10:±0.25 100≥ >30:±0.3 ANGLES:±3°		PRODUCT SPEC 製品规格 APPLICATION SPEC 取付適用规格	SIZE A3	CAGE CODE 00779	DRAWING NO 番号 C=6318157
MATERIAL 材料		FINISH 仕上	WEIGHT	RESTRICTED TO	
CUSTOMER DRAWING			SCALE 尺度 4:1	SHEET 3 OF 6	


REVISIONS					
変更					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-




280P



240P



320P




200P

OBSOLETE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
單位: 耗
mm



MATERIAL
材料

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
一般公差

- 0 PLC ± -
- 1 PLC ± -
- 2 PLC ± -
- 3 PLC ± -
- 4 PLC ± -
- ANGLES ± -

FINISH
仕上

DWN
CHK
APVD
PRODUCT SPEC 製品規格
APPLICATION SPEC 取付適用規格
WEIGHT



TE Connectivity Ltd.		NAME 名称		RESTRICTED TO
		SOFT TRAY ASSY FH 0.6BTB CONNECTOR REC 4H W/G-CONT 2ROW TYPE		
SIZE A3	CAGE CODE 00779	DRAWING NO 番号 G=6318157		

GENERAL TOLERANCE
一般公差

10 ≥: ±0.2
 30 ≥ >10: ±0.25
 100 ≥ >30: ±0.3
 ANGLES: ±3°

CUSTOMER DRAWING	SCALE 尺度 3:1	SHEET 4 OF 6	REV B
------------------	-----------------	-----------------	----------

REVISIONS					
変更					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-




REFERENCE P.C.BOARD LAYOUT

OBSOLETE

AVAILABLE	51.8	50.6	54.7	50	47.4	160
AVAILABLE	45.8	44.6	48.7	44	41.4	140
NOT AVAILABLE	39.8	38.6	42.7	38	35.4	120
AVAILABLE	33.8	32.6	36.7	32	29.4	100
TOOLING STATUS	E	D	C	B	A	POS

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN		TE Connectivity Ltd.	
DIMENSIONS: 單位: 耗 mm		CHK			
TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差		APVD		NAME 名称	
0 PLC ± 0.3 1 PLC ± 0.3 2 PLC ± 0.3 3 PLC ± 0.3 4 PLC ± 0.3 ANGLES ± 3°		PRODUCT SPEC 製品規格		SOFT TRAY ASSY	
MATERIAL 材料		WEIGHT		FH 0.6BTB CONNECTOR	
FINISH 仕上		CUSTOMER DRAWING		REC 4H W/G-CONT 2ROW TYPE	
①		A3 00779		DRAWING NO 番号	
②		G=6318157		RESTRICTED TO	
		SCALE 尺度 4:1		SHEET 5 OF 6	
				REV B	

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
-		SEE SHEET 1	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	TE Connectivity Ltd.	
DIMENSIONS: 单位: 耗 mm		CHK		
TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差		APVD	SOFT TRAY ASSY	
0 PLC ± 0.3 1 PLC ± 0.3 2 PLC ± 0.3 3 PLC ± 0.3 4 PLC ± 0.3 ANGLES ± 3°		PRODUCT SPEC 製品规格	FH 0.6BTB CONNECTOR	
MATERIAL 材料		APPLICATION SPEC 取付適用规格	REC 4H W/G-CONT 2ROW TYPE	
FINISH 仕上		WEIGHT	SIZE A3	RESTRICTED TO
		CUSTOMER DRAWING	CAGE CODE 00779	DRAWING NO 番号 G=6318157
			SCALE 尺度 3:1	SHEET 6 OF 6
				REV B