



产品认证证书

证书编号: CQC16002154262

发证日期: 2024年06月13日
有效期至: 2029年06月12日

委托人名称 TE Connectivity Austria GmbH
及注册地址 Schrackstrasse 1 3830 Waidhofen / Thaya Austria

制造商名称 TE Connectivity Austria GmbH
及注册地址 Schrackstrasse 1 3830 Waidhofen / Thaya Austria

生产企业名称 TE Connectivity Trutnov s.r.o.
及生产地址 Komenského 821 CZ-541 83 Trutnov Czech Republic

产品名称和系列、规格、型号 继电器
RY 系列, 触电负载: 8A 250VAC; 线圈: 5VDC、6VDC、8VDC、9VDC、10VDC、12VDC、15VDC、18VDC、19VDC、21VDC、24VDC、32VDC、36VDC、48VDC、60VDC; 0.245W; 电气寿命: 10000 周期 (触点材质 AgCdO、AgNi), 5000 周期 (触点材质 AgSnO); 机械寿命: 30000000 周期; 环境温度: -40°C ~ 70°C; RII、RTIII (系列命名方式见证书附件)

产品标准和技术要求 GB/T 21711.1-2023

认证模式 产品型式试验+初次工厂检查+获证后监督

上述产品符合 CQC11-462155-2010 认证规则的要求, 特发此证。
本证书为变更证书, 证书首次颁发日期: 2016年11月01日
证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

可通过扫描下方二维码或登录国家认监委网站 (www.cnca.gov.cn) 查验证书信息



签发:

谢肇煦



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE





产品认证证书

证书编号: CQC16002154262

第 1 页 / 共 1 页

本证书及附件应同时使用, 信息查验说明见证书页

纸号:

型号命名规则:

	<u>R</u> <u>Y</u>	<u>6</u>	<u>1</u>	<u>1</u>	<u>024</u>	<u>####</u>
	<u>I</u>	<u>II</u>	<u>III</u>	<u>IV</u>	<u>V</u>	<u>VI</u>
I 基本型号	RY					
II 密封性和端子距离	2 开孔, 3.2mm 端子距离 5 开孔, 5mm 端子距离(N.O. or N.C. contact) 6 密封, 3.2mm 端子距离 A 密封, 5mm 端子距离(N.O. or N.C. contact)					
III 触点结构	1 C.O. contact 3 N.O. contact 5 N.C. contact					
IV 触点材质	0 AgCdO	Contact mounting construction			Riveted	
	1 AgNi 0,15				Riveted or Welded	
	2 AgNi 0,15 HTV				Riveted or Welded	
	3 AgSnO				Riveted or Welded	
V 线圈电压 (DC)	005:5V/ 006:6V/ 008:8V/ 009:9V/ 012:12V/ 015:15V/ 018:18V/ 019:19V/ 021:21V/ 024:24V/ 032:32V/ 036:36V/ 048:48V/ 060:60V					
VI 代码	4 位数字或字母代码, 产品上可不显示出来 R 回流焊型号 (2 开孔, 3.2mm 端子距离和 5 开孔, 3.2mm 端子距离)					



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE



CERTIFICATE OF PRODUCT CERTIFICATION

CERTIFICATE NO.: CQC16002154262

Valid from: Jun.13,2024

Valid until:Jun.12,2029

NAME AND REGISTERED ADDRESS OF THE APPLICANT TE Connectivity Austria GmbH
Schrackstrasse 1 3830 Waidhofen / Thaya Austria

NAME AND REGISTERED ADDRESS OF THE MANUFACTURER TE Connectivity Austria GmbH
Schrackstrasse 1 3830 Waidhofen / Thaya Austria

NAME AND LOCATION OF THE FACTORY TE Connectivity Trutnov s.r.o.
Komenského 821 CZ-541 83 Trutnov Czech Republic

PRODUCT NAME, MODEL AND SPECIFICATION Relay
RY series,Contact load:8A 250VAC, Coil:5VDC、 6VDC、 8VDC、 9VDC、 10VDC、 12VDC、 15VDC、 18VDC、 19VDC、 21VDC、 24VDC、 32VDC、 36VDC、 48VDC、 60VDC ; 0.245W; Electrical endurance:10000 cycles(AgCdO、 AgNi contact);5000cycles(AgSnO contact) ; Mechanical endurance : 30000000 cycles; Ambient temperature:-40°C ~ 70°C ; RTII、 RTIII , Series description see the annex

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS GB/T 21711.1-2023

TYPE OF CERTIFICATION SCHEMES Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC11-462155-2010.

Date of original issued: Nov.01,2016

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn



SIGNATURE:

谢肇煦



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE



CHINA QUALITY CERTIFICATION CENTRE CO., LTD.
Section 9, No. 188, Nansihuan Xilu, Beijing 100070 P. R. China

Tel: +86 10 83886666
<http://www.cqc.com.cn>



CERTIFICATE OF PRODUCT CERTIFICATION

CERTIFICATE NO. : CQC16002154262

page 1 of 1

paper:

This certificate and attachments shall be used at the same time, and the verification instructions can be found in the main certificate.

Example ¹⁾	<u>RY</u> ¹⁾	<u>6</u> ²⁾	<u>1</u> ³⁾	<u>1</u> ⁴⁾	<u>024</u> ⁵⁾	<u>###</u> ⁶⁾										
	I ¹⁾	II ²⁾	III ³⁾	IV ⁴⁾	V ⁵⁾	VI ⁶⁾										
I ¹⁾ Basic series ²⁾	RY ³⁾															
II ²⁾ Version(sealing and pin) ³⁾	2	RTII flux proofed, pinning 3,2mm ⁴⁾														
	5	RTII flux proofed, pinning 5,0mm (N.O. or N.C. contact only) ⁴⁾														
	6	RTIII <u>washtight</u> , pinning 3,2mm ⁴⁾														
	A	RTIII <u>washtight</u> , pinning 5,0mm (N.O. or N.C. contact only) ⁴⁾														
III ³⁾ Contact arrangement ⁴⁾	1	1 C.O. contact ⁵⁾														
	3	1 N.O. contact ⁵⁾														
	5	1 N.C. contact ⁵⁾														
IV ⁴⁾ Contact material ⁵⁾	0	AgCdO ⁶⁾	Contact mounting construction ⁷⁾	Riveted ⁸⁾												
	1	AgNi 0,15 ⁶⁾		Riveted or Welded ⁸⁾												
	2	AgNi 0,15 HTV ⁶⁾		Riveted or Welded ⁸⁾												
	3	AgSnO ⁶⁾		Riveted or Welded ⁸⁾												
V ⁵⁾ Coil voltage and coil code ⁶⁾	Coil Voltage / V ⁷⁾		Coil code ⁸⁾													
	DC ⁹⁾	5 ¹⁰⁾	005 ¹¹⁾													
	DC ⁹⁾	6 ¹⁰⁾	006 ¹¹⁾													
	DC ⁹⁾	8 ¹⁰⁾	008 ¹¹⁾													
	DC ⁹⁾	9 ¹⁰⁾	009 ¹¹⁾													
	DC ⁹⁾	12 ¹⁰⁾	012 ¹¹⁾													
	DC ⁹⁾	15 ¹⁰⁾	015 ¹¹⁾													
	DC ⁹⁾	18 ¹⁰⁾	018 ¹¹⁾													
	DC ⁹⁾	19 ¹⁰⁾	019 ¹¹⁾													
	DC ⁹⁾	21 ¹⁰⁾	021 ¹¹⁾													
	DC ⁹⁾	24 ¹⁰⁾	024 ¹¹⁾													
	DC ⁹⁾	32 ¹⁰⁾	032 ¹¹⁾													
	DC ⁹⁾	36 ¹⁰⁾	036 ¹¹⁾													
	DC ⁹⁾	48 ¹⁰⁾	048 ¹¹⁾													
	DC ⁹⁾	60 ¹⁰⁾	060 ¹¹⁾													
VI ⁶⁾ Additional manufacturer indications ⁷⁾	###	May be followed by up to four numbers or/and letters only for manufacturer internal identification ⁸⁾														
	R	Reflow Type For Versions 2 and 5 only (RT II flux proofed) ⁸⁾														



中国质量认证中心
CHINA QUALITY CERTIFICATION CENTRE