



# 产品认证证书

证书编号: CQC18002189312

发证日期: 2024年06月14日  
有效期至: 2029年06月12日

委托人名称 TE Connectivity Austria GmbH  
及注册地址 Schrackstrasse 1 3830 Waidhofen / Thaya Austria

制造商名称 TE Connectivity Austria GmbH  
及注册地址 Schrackstrasse 1 3830 Waidhofen / Thaya Austria

生产企业名称 泰科电子(深圳)有限公司  
及生产地址 深圳市宝安区石岩街道泰科电子科技园

产品名称和系列、规格、型号 继电器  
RZ 系列 触点负载:16A 250VAC ; 12A 24VDC ; 线圈: 3VDC、5VDC、6VDC、9VDC、12VDC、15VDC、18VDC、24VDC、28VDC、34VDC、36VDC、48VDC 0.40W~0.43W ; 电气寿命 : 20000 周期(250VAC) , 1000 周期( 24VDC ) ; 机械寿命 : 200000 周期 ; 环境温度: -40°C ~ 85°C(RZ0 型), -40°C ~ 105°C ( RZH 型 ) ; RTII

产品标准和技术要求 GB/T 21711.1-2023

认证模式 产品型式试验+初次工厂检查+获证后监督

上述产品符合 CQC11-462155-2010 认证规则的要求, 特发此证。  
本证书为变更证书, 证书首次颁发日期: 2018年03月29日  
证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

可通过扫描下方二维码或登录国家认监委网站(www.cnca.gov.cn) 查验证书信息



签发:

谢肇煦



中国质量认证中心  
CHINA QUALITY CERTIFICATION CENTRE





# 产品认证证书

证书编号: CQC18002189312

第 1 页 / 共 1 页

本证书及附件应同时使用, 信息查验说明见证书页

纸号:

型号命名规则:

RZ	0	3	-1	A	4	-D	012	-R	0	0	XXXX	代码: 4 位数字或字母代码 (产品上可表示出来)
												机械特征: 0 或空白-标准型; S- 插座型
												电气特征: 0 或空白-标准型
												封装类型: -R: 加强型防松香
												线圈电压: 3、5、6、9、12、15、18、24、28、 34、36、48VDC, 012-表示 12VDC
												线圈款式: D-直流线圈
												触点材质: 4-AgNi 3-AgSnO <sub>2</sub>
												触点结构: A-A 型 (单刀单掷-常开型)
												极数: 1-1 极
												产品款式: 3-16A, 双端脚 5mm H_16A, 双端脚 5mm, 高性能
												附加型号: 0-标准型 (85℃) H: 高温型 (105℃)
												基本型号: RZ



中国质量认证中心  
CHINA QUALITY CERTIFICATION CENTRE



# CERTIFICATE OF PRODUCT CERTIFICATION

CERTIFICATE NO.: CQC18002189312

Valid from: Jun.14,2024

Valid until:Jun.12,2029

<b>NAME AND REGISTERED ADDRESS OF THE APPLICANT</b>	TE Connectivity Austria GmbH Schrackstrasse 1 3830 Waidhofen / Thaya Austria
<b>NAME AND REGISTERED ADDRESS OF THE MANUFACTURER</b>	TE Connectivity Austria GmbH Schrackstrasse 1 3830 Waidhofen / Thaya Austria
<b>NAME AND LOCATION OF THE FACTORY</b>	Tyco Electronics (shenzhen) Co., Ltd Tyco Electronics Technology Park,Shiyan Town,Baoan District,Shenzhen, Guangdong, P.R.China
<b>PRODUCT NAME, MODEL AND SPECIFICATION</b>	Relay RZ series Contact load: 16A 250VAC,12A 24VDC; coil: 3VDC, 5VDC, 6VDC, 9VDC, 12VDC, 15VDC, 18VDC, 24VDC, 28VDC, 34VDC, 36VDC, 48VDC; 0.40W ~ 0.43W; Electrical Endurance: 20000cycles(250VAC),1000cycles (24VDC); Mechanical endurance:200000cycles; Ambient temperature:- 40°C ~ 85°C(RZ0 series),-40°C ~ 105°C ( RZH series ) ;RTII Series description see the annex
<b>THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS</b>	GB/T 21711.1-2023

**TYPE OF CERTIFICATION SCHEMES** Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC11-462155-2010.

Date of original issued: Mar.29,2018

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

The certificate information is available through the QR code below or CNCA's website: [www.cnca.gov.cn](http://www.cnca.gov.cn)



SIGNATURE:

谢肇煦



中国质量认证中心  
CHINA QUALITY CERTIFICATION CENTRE



CHINA QUALITY CERTIFICATION CENTRE CO., LTD.  
Section 9, No. 188, Nansihuan Xilu, Beijing 100070 P. R. China

Tel: +86 10 83886666  
<http://www.cqc.com.cn>





# CERTIFICATE OF PRODUCT CERTIFICATION


CERTIFICATE NO. : CQC18002189312

page 1 of 1

paper:

This certificate and attachments shall be used at the same time, and the verification instructions can be found in the main certificate.

RZ	0	3	-1	A	4	-D	012	-R	0	0	XXXX	may be followed by up to 4 numbers and/or letters, mark can be on product body.
												Mechanical Features: 0 or balnk -standard; S-socketable
												Electrical Features : 0 or balnk -standard;
												Category of protection: -R: RTII, reinforce flux proofed(flux proof);
												Coil voltage: 3Vdc, 5Vdc, 6Vdc, 9Vdc, 12Vdc, 15Vdc, 18Vdc, 24Vdc, 28Vdc, 34Vdc, 36Vdc, 48Vdc
												Coil version: D- DC coil
												Contact material: 3-AgSnO <sub>2</sub> ; 4-AgNi
												Contact configuration: A- form A (SPST- NO)
												Pole: 1-1pole
												Version: 3-16A, 5mm double pinning; H-16A,5mm double pinning, high performance
												Version: 0-standard(85°C); H-hot version (105°C)
												Type: RZ



中国质量认证中心  
CHINA QUALITY CERTIFICATION CENTRE