

File E28476
Project 76ME5548

Issued: July 15, 1976
Revised: February 3, 2011

REPORT

on

COMPONENT - CONNECTORS FOR USE IN DATA, SIGNAL, CONTROL AND POWER APPLICATIONS

Tyco Electronics Corp.
Harrisburg, Pennsylvania

Copyright © 1976 Underwriters Laboratories Inc.

Underwriters Laboratories Inc. authorizes the above named company to reproduce this Report either in its entirety or the portion of this Report consisting of the Cover Page up to (but not including) the Construction Details Descriptive pages.

File E28476	Vol. 3	Sec. 6	Page 1	Issued: 1976-07-15
	Vol. 4	Sec. 7		Revised: 2024-06-18
	Vol. 7	Sec. 16		
	Vol. 39	Sec. 5		
	Vol. 48	Sec. 1		
	Vol. 52	Sec. 2		
	Vol. 74	Sec. 1		
	Vol. 94	Sec. 12		
	Vol. 68	Sec. 28		
	Vol. 111	Sec. 14		
	Vol. 116	Sec. 4		
	Vol. 132	Sec. 4		
	Vol. 135	Sec. 4		
	Vol. 145	Sec. 1		
	Vol. 147	Sec. 2		

and Report

DESCRIPTION

PRODUCT COVERED:

Component Connectors - USR, Series Universal MATE-N-LOK, Universal MATE-N-LOK Bulkhead.

USR: Universal Mate-N-LOK Connectors, Cat. Nos. 1-350736-9, **794816-1**, **794816-2**, 2029387-1, 1-350777-9, 350810-1, 926307-3, 926308-3, 926309-3, 926302-3, 350735-1, 350783-1, 350784-1, 1-480698-0, 1-480700-0, 1-480701-0, 350780-1, 1-480704-0, 2106127-1, 2106509-X.

USR, CNR: Universal Mate-N-LOK Bulkhead Connector and Mating Connector Series 1604254 and 350720 and Socket Header Cat. Nos. 2029361-1 and 2029402-1; Printed Circuit Board Socket Header Cat. No. 1586892-1; Universal MATE-N-LOK II; Universal Mate-N-LOK Socket Header Cat. No. 1586869-1, 1586893-3. Universal Mate-N-LOK Pin Header Cat. No. 1586953-1. Universal Mate-N-LOK Plug Cat. No. 640581-1,-2. Universal MATE-N-LOK, Cat. Nos. 2106070-1, 350766-1, 2213725-1, 1969881-1, 1969882-1. UNIVERSAL LIGHT-N-LOK Cat. No. 2213727-1, 770262-1, -2, -3, -4.

USR, CNR: Universal Mate-N-LOK Connectors, Cat. No. 794741-1, 2029457-1.

USR, Universal MATE-N-LOK Bulkhead, Cat. Nos. 1877788, 2825081-1. Universal Mate-N-LOK 350792-X, and 350793-X where X = 1, 3, and represents terminal plating (1 = tin, 3 = gold).

USR, Universal MATE-N-LOK Connectors, Headers, Cat. Nos. 2213752-X, 2213753-X, 2213755-X, 2213756-X.

USR, Universal MATE-N-LOK Headers, Cat. Nos. 1969795-1, 1969796-1, 1969797-1, 1969798-1, 1969799-1, 1969800-1, 1969801-1, 1969802-1, 1969803-1, 1969804-1, 1969805-1, 1969806-1, 1969807-1, 1969808-1, 1969809-1, 1969810-1, 1969811-1, 1969812-1, 1969813-1, 1969814-1, 1969815-1, 1969816-1, 1969817-1, 1969818-1, 1969830-1.

USR, CNR - FASTON Series 250, Cat. No. 521785-3

USR, CNR - Universal MATE-N-LOK Twist N-LOK, Cat. No. 2359624-X

USR, CNR - Universal MATE-N-LOK, Cat. No. 2387361-1

File E28476

Vol. 3 Sec. 6
Vol. 4 Sec. 7
Vol. 7 Sec. 16
Vol. 39 Sec. 5
Vol. 48 Sec. 1
Vol. 52 Sec. 2
Vol. 74 Sec. 1
Vol. 94 Sec. 12
Vol. 68 Sec. 28
Vol. 111 Sec. 14
Vol. 116 Sec. 4
Vol. 132 Sec. 4
Vol. 135 Sec. 4
Vol. 145 Sec. 1
Vol. 147 Sec. 2

Page 1-1

Issued: 1976-07-15

New: 2023-09-12

and Report

GENERAL:

The devices are mating multi-pole connectors for use within electrical appliance enclosures. These are factory assembled connectors on wire leads.

USR indicates investigation to United States Standards as referenced in the Test Record.

CNR indicates investigation to Canadian National Standards as referenced in the Test Record.

and Report

RATINGS:

Cat. No.	Wire AWG (str)	Current (A)	Voltage (V)
350779-4, Series 2312156	14, 12	15	600
350780-1, Series 2312157	14, 12	15	600
1604254	16	15 (position #2 and #4) 3.2 (position #7 and #8)	250
350720	16	15 (position #2 and #4) 3.2 (position #7 and #8)	250
1586869-1	-	16	600V ac/dc
1586953-1	-	17	600V ac/dc
2106070-1, 350766-1, 2213727-1, 770262-1, 770262-2, 770262-3, 770262-4, 2213725-1	--	12	600VAC
2213752-X, 2213753-X, 2213755-X, 2213756-X	-	12	600V ac/dc
1-350736-9, 794816-1 794816-2	10	12	600V ac/dc
2029387-1	10	16.5	600V ac/dc
794741-1	16	15 (position #2 and #4) 3.2 (position #7 and #8)	600V ac/dc
1-350777-9	10	19	600V ac/dc
521785-3	14-18	--	--
2387361-1	18	13 USR 12 CNR	600

The Universal MATE-N-LOK II Series has no electrical ratings.

Universal Mate-N-LOK Plug Cat. No. 640581-1,-2 and Universal Mate-N-LOK Socket Header Cat. Nos. 1586893-3, 2232696-1 have no electrical ratings.

FASTON Series 250, Cat. No. 521785-3 has no electrical ratings.

Universal MATE-N-LOK Twist N-LOK, Cat. No. 2359624-X has no electrical ratings.

Universal MATE-N-LOK Header Cat. Nos. 2106127-1, 2106509-X have no electrical ratings.

and Report

ENGINEERING CONSIDERATIONS (NOT FOR UL REPRESENTATIVE USE):

Use - For use only in complete equipment where the acceptability of the combination is determined by Underwriters Laboratories Inc.

Conditions of Acceptability - In order to be judged acceptable as a component of electrical equipment, the following conditions should be met.

1. These devices should be used only where they will not interrupt the current.
2. These devices have not been tested for current-carrying capability except for the following contacts:

	Cat. No.	Wire AWG	Current (A)	Max Temp Rise (°C)
	193796-1, 193797-1	10	22	30.3
	350922-3, 350923-3	12	20	36.1
	350537-1, 350538-1, 1954443-1	(2) 18	10.5	29.7
	350537-1, 350700-1	(2) 18	10.5	33.1
	1586064-1, 1586065-1	10	25	42.0
	1586064-1, 1586065-1	12	24	41.0
	1586067-1, 1586066-1	14	17	52.0
	1586067-1, 1586066-1	20	10	62.0
	881111-1, 881109-1	14	12	79.1
	881111-1, 881109-1	20	8	79.8
	1586096-1, 1586065-1	10	22	26.2
	1586096-1, 1586065-1	12	20	31.6
	1982101	10	30	51.4
	350779-4, 350780-1, Series 2312156, 2312157	14	15	64
	350873-3, 350874-3	16	15	26.9
	1586869-1	14	16	29.95
	1586953-1	14	17	29.45
	2387361-1 (USR)	18	13	35.2
	2387361-1 (CNR)	18	12	28.9

and Report

The following devices have been tested for current-carrying capability.

Housing Cat. No.	Contact Cat. No.	Wire AWG	Current (A)	Max Temp (°C)
1-480704-0, 1-480705-0 (represents 3-480704-0, 794816-1 794816-2)	350536-1, 350218-1	18	11	80.8
1604254-1, 350720-1	350873-3, 350874-3	16	15 (position #2 and #4) 3.2 (position #7 and #8)	51.9

Cat Nos.	Current, A	Maximum Temperature °C	
		Rise	Recorded Temperature
2213725-1 (represents 2106070-1)	12	28.9	53.9
2213727-1 (represents 350766-1)	12	20.6	45.6

Cat Nos.	Socket/Pin Cat. No.	Current, A	Maximum Temperature °C	
			Rise	Recorded Temperature
2213752-5	770528-1	12	36.2	61.2
2213753-5	350574-4	12	38.9	63.9
2231755-4	770528-1	12	49.2	74.2
2213756-4	350574-4	12	53.8	78.8
2387361-1	350654-1	13 (USR)	35.2	60.2
	350654-1	12 (CNR)	28.9	53.9

3. The placement of these devices within the equipment enclosure should be such that spacings between the live parts and the equipment are suitable for the particular application.

and Report

4. The suitability of the insulating materials used in the molded bodies shall be judged in the end-use equipment.

Cat. Nos	Insulating Material (#)	Measured Minimum Thickness	Flame Class	HWI	HAI	RTI Elec, °C	Max operating Temp, °C
2106067-1,-2 2106070-1,-2 2106127-1,-2 2106130-1,-2, 2213725-1, 2106509-x	A	1.14 mm	V-0	0	0	140	120
1950041-x, 2387361-1	B	0.73 mm	V-0	0	0	140	120
794133-1, 794134-1, 794135-1	C	0.84 mm	V-0	2	3	115	100
2029314-x, 2029315-x	D	0.75 mm	V-2	4	0	150	150
1586892-1	E	0.86 mm	V-2	4	0	130	130
794707-1	D	0.51 mm	-	-	-	150	150
1586703-1	F	0.51 mm	V-2	-	-	130	130
Housing 2029367-1	F	0.75 mm	V2	4	0	130	130
Housing 2029368-1	F	0.75 mm	V2	4	0	130	130
Housing 2029369-1	F	0.75 mm	V2	4	0	130	130
Housing 2029370-1	F	0.75 mm	V2	4	0	130	130
1-480698-0, , 1-480700-0, 1-480701-0	F	--	V2	4	0	130	130
1-480704-0, 3-480704-0	F	--	V2	4	0	130	130
1-1703062-2,1-1703061-2,2178474-2,2178473-2,2178773-1,1- 1644055-2,1-1644055-3, 927231-7,1-1863003-2,1-1863006- 2,1-1863005-2,926309-7,1-1863004-2,1586892-3	G	0.4mm	V0	4	0	140	140
Housing Cat. Nos. 926298-1, 926299-1, 926300-1, 926301- 1, 926302-1, 926308-1, 926309-1, 926647-1, 969326-1	H	0.71	V2	4	0	140	140
1586869-1	E	1.15	V-2	4	0	130	130
1586953-1	E	1.15	V-2	4	0	130	130
350809-3	G	0.4 mm	V-0	4	0	140	140
350810-2	G	0.4 mm	V-0	4	0	140	140
926298-7	G	0.4 mm	V-0	4	0	140	140
926305-7	G	0.4 mm	V-0	4	0	140	140
1586893-3, 640581-1,-2	G	0.4 mm	V-0	4	0	140	140
2213727-1, 770262-1,-2,-3,-4	I	0.76 mm	V0	4	0	120	120
Universal Mate N Lok Headers, Cat. Nos. 1969795-1, 1969796-1, 1969797-1, 1969798-1, 1969799-1, 1969800-1, 1969801-1, 1969802-1, 1969803-1, 1969804-1, 1969805-1, 1969806-1, 1969807-1, 1969808-1, 1969809-1, 1969810-1, 1969811-1, 1969812-1, 1969813-1, 1969814-1, 1969815-1, 1969816-1, 1969817-1, 1969818-1, 1969830-1	J	0.4 mm	V0	4	0	120	120
Housing, 2294562-1, -2, 2359624-x	F	0.74 mm	V2	4	0	130	130
2213752-X, 2213753-X, 2213755-X, 2213756-X	K	0.8 mm	V-0	2	0	240	105
1969881-1, 1969882-1	L	0.4mm	V0	0	0	130	130

and Report

Cat. Nos	Insulating Material (#)	Measured Minimum Thickness	Flame Class	HWI	HAI	RTI Elec, °C	Max operating Temp, °C
173924-1, 173925-1, 173926-1	M	0.6 mm	V-0	3	0	140	85
1-350736-9	N	0.60 mm	V-0	4	0	130	120
2029387-1	N	0.60 mm	V-0	4	0	130	120
794741-1	N	0.60 mm	V-0	4	0	130	120
1-350777-9	N	0.60 mm	V-0	4	0	130	120
Universal MATE-N-LOK, Cat. No. 350810-1	N	0.76 mm	V-0	4	0	130	120
Universal MATE-N-LOK, Cat. No. 926307-3, 926308-3, 926309-3	N	0.76 mm	V-0	4	0	130	120
Universal MATE-N-LOK, Cat. No. 926302-3	N	0.64 mm	V-0	4	0	130	120
Universal MATE-N-LOK, Cat. No. 350735-1	N	0.64 mm	V-0	4	0	130	120
Universal MATE-N-LOK, Cat. No. 350783-1, 350784-1	N	0.76 mm	V-0	4	0	130	120
350433-5	L	0.70 mm	V-0	0	0	130	130
521785-3	O	0.4 mm	V0	4	0	130	130
350778-1, 350767-1, 350780-1, 350781-1, 350777-4, 350766-4, 350782-1	P	0.38	V0	4	0	130	130

Vol. 3	Sec. 6
Vol. 4	Sec. 7
Vol. 7	Sec. 16
Vol. 39	Sec. 5
Vol. 48	Sec. 1
Vol. 52	Sec. 2
Vol. 74	Sec. 1
Vol. 94	Sec. 12
Vol. 68	Sec. 28
Vol. 111	Sec. 14
Vol. 116	Sec. 4
Vol. 132	Sec. 4
Vol. 135	Sec. 4
Vol. 145	Sec. 1
Vol. 147	Sec. 2

and Report

- (#) - Code for Insulating Body Material
- A. Tyco 703570-3
 - 1. Dielectric strength (KV/mm): - 23
 - 2. CTI: 2
- B. Tyco 704318
 - 1. Dielectric strength (KV/mm): 26
 - 2. CTI: 1
- C. Tyco 1573672
 - 1. CTI: 0
- D. Tyco 703609
 - 1. CTI: 2
- E. Tyco 705304
 - 1. CTI: 2
- F. Tyco 702925
 - 1. Dielectric strength (kV/mm): 26
 - 2. CTI: 0
- G. Tyco ___1573697
 - Dielectric Strength - --
 - CTI - 2
- H. Tyco 703561___
 - Dielectric Strength - --
 - CTI - 1
- I. Tyco 705287___
 - Dielectric Strength - --
 - CTI - 0
- J. Tyco 2136403
 - Dielectric Strength - --
 - CTI - 2

*

File E28476

Vol. 3 Sec. 6
Vol. 4 Sec. 7
Vol. 7 Sec. 16
Vol. 39 Sec. 5
Vol. 48 Sec. 1
Vol. 52 Sec. 2
Vol. 74 Sec. 1
Vol. 94 Sec. 12
Vol. 68 Sec. 28
Vol. 111 Sec. 14
Vol. 116 Sec. 4
Vol. 132 Sec. 4
Vol. 135 Sec. 4
Vol. 145 Sec. 1
Vol. 147 Sec. 2

Page 5A

Issued: 1976-07-15
Revised: 2019-12-20

and Report

- K. Tyco 1573878
Dielectric Strength - 39
CTI - 4
- L. TE 2136700
Dielectric Strength - 17
CTI - 2
- (#) - Code for Insulating Body Material
- M. TE 2136507
Dielectric Strength - 19
CTI - -
- N. TE 2136597
Dielectric Strength - 13
CTI - 0
- O. TE 2136682
Dielectric Strength - 20
CTI - 0
- P. TE 2136597-2
Dielectric Strength - 13
CTI - 0