


SPECIFICATIONS

INPUT VOLTAGE: 3.0 V rms (NOM)
 INPUT FREQUENCY: 1.8 KHz (NOM)
 ELECTRICAL STROKE: +/- 0.435"
 MECHANICAL STROKE: +/-0.500"
 SENSITIVITY: .78 mv/V/.001"
 LINEARITY: 0.5% OF FULL RANGE OUTPUT
 PHASE SHIFT: 43 DEG. .
 IMPEDANCE:
 PRIMARY: 150 OHMS (NOM)
 SECONDARY: 225 OHMS (NOM)
 OPERATING TEMPERATURE: -65 C (-85 F) TO 135 C (265 DEG. F)


REVISIONS

REV.	DESCRIPTION	DATE:	APPR.
A	CHANGED PER E99813 DESIGN REVEIW	10 05 99	R.E.A.
B	CHANGED PER ECR/ECN #334	04/02/01	R.E.A.
C	CHANGED PER ECR/ECN #386	07/02/01	R.E.A.
D	REVISED PER ECR/ECN #491	04/05/02	R.E.A.
D1	REDRAWN WITH NO CHANGES	24/08/20	

(5) #28 AWG LEADS, TEFLON INSUL.
MINIMUM LENGTH 8 INCHES



#2-56 UNC-2A THD



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE IN INCHES

TOLERANCES ARE:
 ANGLES: +/- 0.5 DEG.
 FRACTIONS: +/- 1/64 .
 DECIMAL:
 XX= +/- .01
 .XXX= +/- .005

This Drawing and Specifications are the property of Macro Sensors, Div. of Howard A. Schaevitz Technologies, Inc. DO NOT COPY without the written approval of Macro Sensors.

DRAFTSMAN: R.E.A.	DATE: 16 DEC 98
CHECKER:	DATE:
APPROVED:	DATE:
APPROVED:	DATE:
APPROVED:	DATE:



EVERY CONNECTION COUNTS

TITLE CD 375 500-0373
OUTLINE

A	C.A.G.E. No. 06WW0	DRAWING No. 015912392000
	SHEET No. 1 of 1	

SCALE: NONE

MATERIAL: