



Raychem Metal-Oxide Low Voltage Arresters

Raychem
from TE Connectivity

Raychem Metal-Oxide Low Voltage Arresters



Transition: insulated overhead lines to cables

Raychem low voltage surge arresters provide protection for low-voltage overhead lines, consumer in-house supplies, distribution transformers and other systems. The gapless metal-oxide varistor incorporated in the surge arrester reliably imposes low-value limits on surges caused by atmospheric overvoltages and switching transients, thus protecting the insulation of the consumer-side networks and equipment. The varistor has a very short response time (typically <math><100\text{ ns}</math>) and can safely handle high-current impulses up to 100 kA, 4/10 μs . The arrester's nominal discharge current is 10 kA. The metal-oxide varistor is enclosed in a sturdy, weatherproof polymer housing. Numerous tests have confirmed the durability of the housing, even when exposed to extreme temperature fluctuations and contamination. The LVA surge arresters are in compliance with requirements Class II as defined by IEC 61643-1.



Service entry through overhead system



Overhead line

They are designed for applications in which protection against direct contact is not necessary. Special insulated adapter modules are available for use in insulated overhead-line systems and the low-voltage bushings of distribution transformers.

The integral disconnecter disconnects the arrester from the network if an overload occurs, caused, for example, by a lightning strike in the vicinity or an impermissible voltage excursion in the system. If this happens the rating plate on the underside of the arrester dislocates and remains dangling from a holding wire. The ground connection itself remains securely in position.



Distribution transformers

This arrangement ensures that when the arrester disconnects, the ground connection line cannot penetrate dangerous parts of the overhead system. The rating plate is large and is reflective on the reverse, so the defective arrester is easily spotted. All terminals are made of high-grade steel and connect to aluminum or copper without corrosion problems.

Operation including disconnecter and indicator

Normal operating condition

Fault - arrester disconnected from system



Product features:

- Suitable for indoor and outdoor use
- Integrated disconnecter and 1 m line lead
- Overhead lines housing and lead are flame retardant and UV resistant
- Easy to identify failure indicator
- Easy to install (no tools required)
- Large selection of standard accessories
- CE certified
- Tested according IEC 61643-1 + Amd.1 and EN 61643-11

Technical data

Residual voltage (kV)

Type	Continuous voltage		Lightning current impulse 8/20 μ s					
	U_c (V)		1 kA	2 kA	5 kA	10 kA	20 kA	
LVA-280 B	280		0.73	0.77	0.85	1.0	1.1	no lead (Acc. S)
	280		0.76	0.82	0.96	1.2	1.58	with 15 cm lead
LVA-440 B	440		1.26	1.32	1.44	1.6	1.79	no lead (Acc. S)
	440		1.29	1.38	1.55	1.8	2.21	with 15 cm lead

Metal-oxide surge arresters (SPD)

Class II (IEC 61643-1)	
Nominal discharge current I_n	10 kA
Maximum discharge current I_{max}	40 kA
High current impulse 4/10 μ s	100 kA*
Energy absorption capability	4.1 J/V · U_c
Rated frequency	48 - 62 Hz a.c.
Ambient temperature	-40 ... +70 °C
Max. altitude	2000 m

* Test as per IEC 60099-4

Ordering information

Dimensions (mm)



Accessories for LVA arresters


Line connection



Surge arrester continuous/rated voltage (V)



Ground lead









Ordering example: LVA-280B-BL

Surge arrester for continuous/rated voltage 280V for connection to bare conductor and with insulated stranded earth wire (6 mm²)

Contact us for further information at: surgearrester@te.com

Other products available from TE Energy

<p>Asset protection</p>	<p>Insulation enhancement systems for substations and overhead lines. Designed to prevent unplanned outages due to accidental bridging and to help upgrade insulation levels at critical points in systems.</p> <p>Contact us at: assetprotection@tecom</p>	
<p>Low-voltage surge arresters</p>	<p>LV arresters are used to provide protection for LV overhead lines, consumer in-house supplies, distribution transformers and other appliances.</p> <p>Contact us at: surgearresters@te.com</p>	
<p>Medium-voltage surge arresters</p>	<p>Metal oxide varistor distribution arresters for indoor and outdoor applications for protection of overhead lines, DC locomotives and switchgear applications.</p> <p>Contact us at: surgearresters@te.com</p>	
<p>High-voltage surge arresters</p>	<p>Porcelain and polymeric series parallel and single column constructed arresters for protection of transmission systems up to 550 kV.</p> <p>Contact us at: hvsa@te.com</p>	
<p>Polymeric insulators</p>	<p>Insulators and insulating components/housings providing reliable solutions for power utilities and railway customers with installations in high pollution environments and applications up to 400 kV.</p> <p>Contact us at: insulators@te.com</p>	
<p>Porcelain insulators</p>	<p>Insulators for applications up to system voltages of 132 kV. This range of insulators offers a cost-effective solution for low and medium polluted environments.</p> <p>Contact us at: insulators@te.com</p>	

While TE Connectivity (TE) has made every reasonable effort to ensure the accuracy of the information in this catalog, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications. Raychem, TE Connectivity and TE connectivity (logo) are trademarks. Other logos, product and company names mentioned herein may be trademarks of their respective owners. © 2014 TE Connectivity family of companies. All Rights Reserved

TE Energy – innovative and economical solutions for the electrical power industry: cable accessories, connectors & fittings, insulators & insulation, surge arresters, switching equipment, street lighting, power measurement and control.

LV/MV Product Management
 TE Connectivity Limerick
 International Science Centre
 Block 1, University Of Limerick (N.T.P.)
 Castletroy
 Co. Limerick. Ireland

Phone: + 353 61 470 800
 Email: surgearresters@te.com

energy.te.com

