







keyway opposite keyway




Mounting Detail

with locking ring

without locking ring



Third Angle Projection



	Date	Name	mm	Scale	 Elektrotechnik - GmbH & Co KG D - 72218 Wildberg	Drawing No:
Drawn	17.08.2005	Braun		1:1		08-2-1-16 M
Check	05.12.2005	Braun	General Tolerances DIN ISO 2768 mK		NSN:	5930-12-308-7074

Circuit Diagram

	Circuitry made with toggle at		
	keyway	center	opposite keyway
Pole 1			
Pole 2			

Actuation

- momentary keyway side
- locking center position
- locking opposite keyway side

Locking Configuration

- locked in keyway side
- locked between center position and opposite keyway side

Construction

- Material, Casing Duroplast GF
- Material, Cover GD-ZnAl4Cu1
- Connections Screws M3,5x6 ISO 1580
- Protection Interior IP 6K7 DIN 40 050 Part 9
- Connections IP 00 DIN 40 050 Part 9

Mechanical Data

- Current carrying parts CuZn-Alloy
- Contacts Ag
- Ambient Temperature Range -55°C to +85°C
- Storage Temperature Range -65°C to +85°C
- Life Cycle iaw VG 95 210 Part 21, grade H 100.000 operations

Electrical Data

- Voltage 28 V DC ohmic Load 18A
- 28 V DC inductive Load at L/R = 5 ms 10A
- 28 V DC lamp Load 5A
- 115 V AC ohmic Load 11A
- 115 V AC inductive Load cos. Φ = 0,75, 8A
- 115 V AC lamp Load 2A
- Motor Load utilisation category AC3 (see DIN VDE 0660 Part 107) 5A

Min. Rating 12 V DC, 20 mA

It is recommended to use gold-plated contacts for lower currents or voltages.

	Date	Name	mm ←→	Scale 1:1		Drawing No:
Drawn	17.08.2005	Braun	General Tolerances			Elektrotechnik - GmbH & Co KG
Check	17.08.2005	Braun			D - 72218 Wildberg	NSN.: 5930-12-308-7074