

4

3

2

1

COMPONENT	MATERIAL	FINISH
HOUSING COUPLING NUT	STAINLESS STEEL PER ASTM-A-484 OR ASTM-A-582 TYPE 303	PASSIVATED PER ASTM-A-380
DIELECTRIC	PTFE FLUOROCARBON PER ASTM-D-1457	---
CENTER CONTACT	BERYLLIUM COPPER PER ASTM-B-196 OR 197 ALLOY C17300, CONDITION H	GOLD PLATED PER ASTM-B-488
---	---	---
GASKET	SILICONE RUBBER PER ZZ-R-765	---
FERRULE	COPPER OR BRASS ALLOY, ROCKWELL F65 MAX	GOLD PLATED PER ASTM-B-488
RETAINING RING	BERYLLIUM COPPER PER ASTM-B-194 ALLOY C17200, CONDITION H	---
---	---	---
---	---	---

ENVIRONMENTAL

TEMPERATURE RATING: -65°C TO +165°C

VIBRATION: MIL-STD-202, METHOD 204, CONDITION D

SHOCK: MIL-STD-202, METHOD 213, CONDITION 1

MOISTURE RESISTANCE: MIL-STD-202, METHOD 106

CORROSION: MIL-STD-202, METHOD 101, CONDITION B. 5% SALT SPRAY

THERMAL SHOCK: MIL-STD-202, METHOD 107, CONDITION B EXCEPT HIGH TEMP 85°C

MECHANICAL

INTERFACE DIMENSIONS: MIL-STD-348A FIG. 310.1

RECOMMENDED MATING TORQUE: 7-10 IN-LBS

FORCE TO ENGAGE & DISENGAGE (IN-LBS MAX): 2.0

WEIGHT (GRAMS): TBD

MATING CHARACTERISTICS: INSERTION (MAX LBS) N/A  
WITHDRAWAL (MIN OZ): N/A

CABLE RETENTION: AXIAL FORCE (LBS) 45 MIN  
TORQUE (IN-OZ): N/A

CENTER CONTACT CAPTIVATION: AXIAL (LBS): 6.0  
RADIAL (IN-OZ): N/A

ELECTRICAL

NORMAL IMPEDANCE (OHMS): 50

FREQUENCY RANGE (GHz): DC TO 12.4

VOLT RATING @ SEA LEVEL (VRMS MAX): 335

VSWR: 1.15+.01f(GHz)

INSERTION LOSS: (dB MAX): .06  $\sqrt{f(\text{GHz})}$

RF LEAKAGE (dB MIN): -60 @ 2-3 GHz

CORONA 70,000 FT (VRMS MIN): 250

DIELECTRIC WITHSTANDING VOLTAGE (VRMS MIN) AT SEA LEVEL: 1000

I.R. (MEGOHMS MIN): 5,000

RF HIGH POTENTIAL AT SEA LEVEL (VRMS MIN @ 5 MHz): 670

CONTACT RESISTANCE (MILLIOHMS MAX):  
CENTER CONTACT: 3.0  
OUTER CONTACT: 2.0  
CABLE TO HOUSING: 0.5

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
DF	XO	REV PER 0G3D-0423-02	9-02	JMK	JL

AS SHIPPED TO CUSTOMER

1.375 [34.93] MAX

.570±.020 [14.48±0.51]

.330 [8.38]

FERRULE

DIELECTRIC  
CENTER CONTACT  
GASKET  
RETAINING RING

COUPLING NUT

.312 [7.92] HEX

HOUSING

CABLE  
(CUSTOMER SUPPLIED)

ASSEMBLED VIEW

DESIGNED TO USE RG-223/U OR EQUIVALENT CABLE ENTRY DIAMETER MIN	
HOUSING:	.121 [3.07]
CONTACT:	.039 [0.99]
---	---
---	---
FERRULE:	.216 [5.48]

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
INCHES [mm]			
0 PLC	± -	0 PLC	± -
1 PLC	± -	1 PLC	± -
2 PLC	± -	2 PLC	± -
3 PLC	± .005 [0.13]	3 PLC	± .005 [0.13]
4 PLC	± -	4 PLC	± -
ANGLES	± -	ANGLES	± -
MATERIAL	SEE TABLE	FINISH	SEE TABLE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	9/09/02	tyco Electronics		Tyco Electronics Corporation Harrisburg, PA 17105	
CHK	J. KAISER	10-9-02		NAME			
APVD	J. LIPPERT	10-9-02		PRODUCT SPEC			
APPLICATION SPEC				408-4935			
WEIGHT				TBD	A2 00779		C-1051808
CUSTOMER DRAWING				SCALE	5:1	SHEET	1 OF 1

1051808-1  
PART  
NO.

AMP 1471-9 REV 31MAR2000

J:\DEPT1733\U.DIES\john lippert\1051777\_1\_c.dwg

MA/COM # 2031-8123-92

1051808

B

A