



WARNING - THIS DOCUMENT CONTAINS TECHNOLOGY WHOSE EXPORT IS RESTRICTED BY THE EXPORT ADMINISTRATION REGULATIONS ("EAR") PURSUANT TO 15 C.F.R. PARTS 730-774. VIOLATIONS OF THE EAR ARE SUBJECT TO SEVERE CRIMINAL PENALTIES UNDER THE EXPORT CONTROL REFORM ACT, AS AMENDED (TITLE 50, U.S.C., SEC. 4801, ET SEQ.).

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D	CORRECTION OF MISTAKEN DIM ENVELOPE	27/07/11	MJG	JA
	E	REV PER ECN-24-277916	02AUG2024	LP	JG



- NOTES:
- FOR USE WITH RG-400U KX23 CABLE
 - INSTRUCTION SHEET: 408-1799-5



RECOMMENDED CABLE PREPARATION

SPLIT WASHER	BRASS PER ASTM B36	SILVER PLATE PER ASTM B700
SPRING	BeCu PER ASTM B194	TIN PLATE PER ASTM B545
COLLAR	BRASS PER ASTM B16	SILVER PLATE PER ASTM B700
CENTER MALE CONTACT	BRASS PER ASTM B16	GOLD PLATE PER ASTM B488 OVER NICKEL PLATE PER SAE-AMS-QQ-N-290
FRONT SHELL	BeCu PER ASTM B196	SILVER PLATE PER ASTM B700
RIGHT ANGLE SHELL	BRASS PER ASTM B16	SILVER PLATE PER ASTM B700
CRIMP END SHELL	BRASS PER ASTM B16	SILVER PLATE PER ASTM B700
DIELECTRICS	PTFE FLUOROCARBON PER ASTM-D-1457	N/A
CONTACT FEMALE	BeCu PER ASTM B196	GOLD PLATE PER ASTM B488 OVER NICKEL PLATE PER SAE-AMS-QQ-N-290
CRIMP FERRULE	COPPER OR BRASS ALLOY ROCKWELL B 45 MAX	SILVER PLATE PER ASTM B700
GASKETS	SILICONE RUBBER PER A-A-59588	N/A
COMPONENT	MATERIAL	FINISH

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. GREENER 26JUL2006	 TE Connectivity		
DIMENSIONS:		CHK J. AMBROSE 26JUL2006			
mm		APVD J. AMBROSE 26JUL2006			
		PRODUCT SPEC 108-12002			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	NAME BNC SERIES RIGHT ANGLE PLUG SINGLE CRIMP		
0 PLC ±			SIZE	CAGE CODE	DRAWING NO
1 PLC ±0.3			A2	00779	C-1236009
2 PLC ±0.3			RESTRICTED TO		
3 PLC ±0.3			-		
4 PLC ±					
ANGLES ±1					
FINISH					
MATERIAL SEE TABLE		WEIGHT			
-					
		CUSTOMER DRAWING			
		SCALE 4:1			
		SHEET 1 OF 1			
		REV E			