

THIS DRAWING IS UNPUBLISHED.






RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

© COPYRIGHT - By -

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL REL. PER LC20-0186-10	27OCT2010	DM	AB
	A1	LC20-0025-17 / ECO-17-003184	01MAR2017	DM	BJ



ALTERNATE MARKING ON WEDGE

WEDGE ID.	WIRE SIZE	PART NO.
75	1033.5 TO 266.8	1-1443454-0
74	1033.5 TO 336.4	1443454-9
73	1033.5 TO 397.5	1443454-8
64	1033.5 TO 477.0	1443454-7
72	1033.5 TO 556.5	1443454-6
15	1033.5 TO 636	1443454-5
14	1033.5 TO 715.5	1443454-4
67	1033.5 TO 795	1443454-3
13	1033.5 TO 954	1443454-2
12	1033.5 TO 1033.5	1443454-1

- 1 CORRESPONDING WIRE SIZES TO RUN AND TAP SIDES ARE MARKED ON WEDGE. SEE TABLE FOR DETAILS.
- 2 INHIBITOR IS APPLIED AT FACTORY TO GROOVES OF 'C' BODY AND WEDGE.
- 3. DIMENSIONS ARE FOR REFERENCE ONLY.
- 4. USE YELLOW CARTRIDGE PART NO: 69338-4 WITH AMPACT TOOL PART NO: 69611.
- 5 "HOT SURFACES" IDENTIFICATION SYMBOL AS PER IEC 417 IS INK STAMPED ON CONNECTOR BODY.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. MURUGIAH 27OCT2010	<b>TE Connectivity</b>				
DIMENSIONS: mm [INCH]		CHK A. MARC 28OCT2010				NAME <b>WEDGE TAP CONNECTOR, 1033.5 SERIES, YELLOW CODED, HIGH TEMP, AMPACT</b>	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD B. JOHNSON 28OCT2010	SIZE	CAGE CODE	DRAWING NO		
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC -	A3	00779	C-1443454	-	
MATERIAL ALUM ALLOY		FINISH -	WEIGHT 0	CUSTOMER DRAWING			SCALE NTS
			SHEET 1 OF 1		REV A1		