



P	LTR	DESCRIPTION	DATE	DWN	APVD
A6		ECR-21-003841	31MAR2021	SK	AN
A7		ECR-21-004821	26APR2021	KG	PNI
A8		ECR-21-109980	16AUG2021	SK	AN
A9		ECR-21-117769	19OCT2021	KG	AN

PCB LAYOUT
LEITERPLATTEN-LAYOUT





Notes:
Bemerkungen:

- △ 1 1.27-2.54 μm Ni OVER THE COMPLETE LENGH
1.27-2,54 μm Ni ueber die gesamte Laenge
- △ 2 2-3 μm Sn
- △ 3 0.8-1.8 μm Sn
- △ 4 Sn
- △ 5 Min. 0.8 μm Au




PLATED THROUGH HOLE SPECIFICATION Spezifikation furr durchplatierte Bohrungen	
Cu THICKNESS Kupferschichtdicke	25-50 μm
Sn THICKNESS Zinn-Schichtdicke	4-15 μm
DRILLED HOLE Ø1.5 ±0.025 Bohrungs-Ø 1.5 ±0.025	FINISHED HOLE Ø1.29 +0.15 Platierter Loch-Ø 1.29 +0.15

- △ 7 DIMENSION OF LOOSE PIESE
Mass fuer Einzelteil
- △ 8 TO BE REELED ON PANCAKE REEL WITH INTERLEAVING PAPER
Pappspulen mit Zwischenlagenpapier
- △ 9 TO BE REELED ON PLASTIC REEL WITH INTERLEAVING PAPER
Kunststoffspulen mit Zwischenlagenpapier
- △ 10 3-5 μm Ag
- △ 11 TO BE REELED ON HARD FIBER REEL WITH INTERLEAVING PAPER
Hartfaserspulen mit Zwischenlagenpapier
- ⬡ A9 △ 12 PUNCH MARK, BOTH SIDES
Koernerpunkt, beidseitig




DIRECTION OFF TOP OF REEL



- 1-1452688-2
- 1-1452688-3
- 1-1452688-4
- 2-1452688-1
- 3-1452688-1
- 3-1452688-2

A9	TE PART NO.	REV.	PUNCH MARK	MATERIAL	SURFACE	REEL PACKING
⬡ A9	3-1452688-6	A	△ 12	CuSn4	△ 3 △ 10 OVER △ 1	△ 9
⬡ A9	3-1452688-5	A	△ 12	CuSn4	△ 3 △ 10 OVER △ 1	△ 8
⬡ A9	3-1452688-2	A		CuSn4	△ 3 △ 10 OVER △ 1	△ 9
⬡ A9	3-1452688-1	A		CuSn4	△ 3 △ 10 OVER △ 1	△ 8
	2-1452688-1	A		CuSn4	△ 3 △ 5 OVER △ 1	△ 9
	1-1452688-4	A		CuSn4	△ 2 △ 3 △ 4 OVER △ 1	△ 11
	1-1452688-3	A		CuSn4	△ 2 △ 3 △ 4 OVER △ 1	△ 9
	1-1452688-2	A		CuSn4	△ 2 △ 3 △ 4 OVER △ 1	△ 8

THIS DRAWING IS A CONTROLLED DOCUMENT.



DIMENSIONS:
mm

DWN H.-J. Arnold 13SEP2002
CHK J.Ryll 13SEP2002
APVD 114-18280
PRODUCT SPEC 108-18644
APPLICATION SPEC 114-18280
WEIGHT -
CUSTOMER DRAWING

STE TE Connectivity

NAME TAB 2.8x0.8 WITH ACTION PIN
Flachstecker 2.8x0.8 mit Action Pin

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	©-1452688	-

SCALE 10:1 SHEET 1 OF 1 REV A9