




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
C3		REVISED PER ECR-16-011494	20JUN2017	NK CX
C4		REVISED PER ECO-20-010933	05AUG2020	WLS VS
C5		REVISED PER ECN-23-198901	17FEB2023	WLS VS
C6		REVISED PER ECN-23-242776	14DEC2023	WLS VS



CIRCUIT NUMBER 1
 0.15
 INCLUDES CONTACT TAILS,
 HOUSING STANDOFFS,
 AND BOARDLOCKS.



- 1 MATERIAL: HOUSING - UL 94V-0 RATED HIGH TEMP NYLON, COLOR BLACK.
 CONTACTS - BRASS
 HOLDDOWNS - PHOSPHOR BRONZE.
- 2 RECOMMENDED PC BOARD THICKNESS OF 1.57.
- 3 PLATING: CONTACTS - 2.54µm MINIMUM TIN OVER 1.27µm MINIMUM NICKEL.
 HOLDDOWNS - 2.54µm MINIMUM TIN OVER 1.27µm MINIMUM NICKEL.
- 4 COUNTERPART RECOMMENDED IS PN 1445022 OR 2008571 (DASH ACC. TO NUMBER OF POSITION).
- 5 FOR REELING DIRECTION AND PACKAGING TYPE, SEE SPECIFICATION 114-13000.

OBSOLETE	33.00	40.27	40.00	12	3-1445057-2
OBSOLETE	30.00	37.27	37.00	11	3-1445057-1
	27.00	34.27	34.00	10	3-1445057-0
OBSOLETE	24.00	31.27	31.00	9	2-1445057-9
	21.00	28.27	28.00	8	2-1445057-8
	18.00	25.27	25.00	7	2-1445057-7
	15.00	22.27	22.00	6	2-1445057-6
	12.00	19.27	19.00	5	2-1445057-5
	9.00	16.27	16.00	4	2-1445057-4
	6.00	13.27	13.00	3	2-1445057-3
	3.00	10.27	10.00	2	2-1445057-2
	DIM Z	DIM V	DIM W	NO. OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN	J. ROOT	03-OCT-2000
CHK	K. WHITAKER	13-MAR-2001
APVD	K. WHITAKER	13-MAR-2001
PRODUCT SPEC	108-1836	
APPLICATION SPEC	114-13000	
WEIGHT	-	

STE TE Connectivity

NAME: RT ANGLE SURFACE MOUNT HEADER ASSY, TIN CONTACTS W/SURF MOUNT HOLDDOWNS, SINGLE ROW, MICRO MATE-N-LOK™

SIZE: A2 CAGE CODE: 00779 DRAWING NO: C-1445057 RESTRICTED TO

CUSTOMER DRAWING SCALE: 4:1 SHEET 1 OF 2 REV: C6

4

3


2

1


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
-	-	SEE SHEET 1	-	-


2 POS.




8 POS.




3 POS.




9 POS.




4 POS.




10 POS.




5 POS.




11 POS.





6 POS.



12 POS.





7 POS.

Dimensions shown:
 DIM Z: 3.00 TYP
 1.27±0.08 TYP
 2.92±0.08
 1.65±0.08
 5.48
 3.635
 DIM V
 3.43±0.08
 2 PLC

PCB LAYOUT COMPONENT SIDE 

KEYING BY POSITION SIZE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. ROOT 03-OCT-2000	 TE Connectivity	
DIMENSIONS: mm		CHK K. WHITAKER 13-MAR-2001		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD K. WHITAKER 13-MAR-2001	NAME RT ANGLE SURFACE MOUNT HEADER ASSY, TIN CONTACTS W/SURF MOUNT HOLDDOWNS, SINGLE ROW, MICRO MATE-N-LOK	
		PRODUCT SPEC 108-1836	RESTRICTED TO	
MATERIAL		APPLICATION SPEC 114-13000	SIZE A200779	CAGE CODE C-1445057
FINISH		WEIGHT	SCALE 4:1	SHEET 2 OF 2
-		CUSTOMER DRAWING	REV C6	

1471-9 (3/13)