


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
	A1	ECR-15-017371	30Nov2015	NH SK



- 1 CAVITY 19 FILLED WITH EPOXY.
- 2 CUSTOMER PN AND DATE CODE (YYWW) ARE PRINTED ON THE CONNECTOR SHELL.
- 3 SPECIFICATION:
 - a. ELECTRICAL:
 - CONTACT RESISTANCE : AVG. MATED CONTACT RESISTANCE IS 4 mΩ WITH A MAX VALUE OF 8 mΩ
 - INSULATION RESISTANCE : > 5,000 MΩ AT ROOM TEMPERATURE
 - CURRENT RATING : 3 AMP MAX. PER CONTACT
 - b. MECHANICAL:
 - CONTACT ENGAGING FORCE : 2.22 N MAX. PER CONTACT
 - CONTACT SEPARATION FORCE: 0.14 N MIN. PER CONTACT
 - c. ENVIRONMENTAL:
 - OPERATING TEMPERATURE : -55° C TO +125° C
 - VIBRATION CHARACTERISTICS : PER MIL-STD-202C, METHOD 204-A, CONDITION D
- 4 MATERIAL:
 - INSULATOR : GLASS FILLED PA
 - POTTING COMPOUND : EPOXY
 - CONTACT : COPPER ALLOY, COPPER POSTS
- 5 FINISH:
 - CONTACT : GOLD PLATE PER MIL-G-45204, TYPE II, POSTS TINNED OVER APPROXIMATELY 1 MM
 - HARDWARE : PASSIVATE PER QQ-P-35

6. RESTRICTED TO SAGEM

185926566-02	MCJB2-26SX	21014750-0	1495719-1
CUSTOMER PART NO.	MICRODOT REFERENCE	CUSTOMER DRAWING	TE PN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	SUNNY S	24JAN2013	STE TE Connectivity
DIMENSIONS: mm		CHK	PETRONIN Y	24JAN2013	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	PETRONIN Y	24JAN2013	
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC	NAME		
MATERIAL		FINISH	CONNECTION SPEC		CONNECTOR, JACKMATE, SOCKET, 26 POSITION
4		5		WEIGHT	RESTRICTED TO
CUSTOMER DRAWING		SCALE	NTS	SHEET	1 OF 1
		SIZE	A3	CAGE CODE	00779
		DRAWING NO	G-1495719		REV
				APVD	A1