

THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION

REVISIONS

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

P	LTR	DESCRIPTION	DATE	DWN	APVD
B1	ECR-20-000880		17JAN2020	WZ	WY



NOTES:

1. CABLE IDENTIFICATION AND PACKAGING LABELING ACCORDING TO CISCO SPECIFICATION 95-5583-01 REV. C0. CISCO VENDOR CODE IS 76798 AND THE VENDOR ID IS TYC FOR SUPPLIER TE. CABLE IDENTIFICATION LABEL INFORMATION AS SHOWN BELOW,

CUSTOMER P/N Rev.*
76798 TYC MMY
Made in **** ← Country of Origin

- 2. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TYCO ELECTRONICS STANDARD 230-702.
- 3. ELECTRICAL TEST:
 - A. CONTACT RESISTANCE: 1.0 OHM (MAX)
 - B. INSULATION RESITANCE: 50M OHM (MIM)
 - C. HI-POT TEST: 300V DC 0.01 SEC (MIN)

P1	COLOR	P2
1	WHITE/ORANGE	1
2	ORANGE	2
3	WHITE/GREEN	3
6	GREEN	6
4	BLUE	4
5	WHITE/BLUE	5
7	WHITE/BROWN	7
8	BRN	8

TE P/N: 1521822-1
CUSTOMER P/N:37-0892-01 Rev.A0

AR	MR	DESCRIPTION	ITEM
1	PC	CAT5,UTP,26AWG*4P,E188601,UL,CM,LL84201,CSA,CMG,FT4,60°C	3
1	PC	LABEL, SIZE: 25.0*35.0MM, WHITE: 25.0*13.0MM.	2
2	PC	MJPLUG, 8P, ROUND, 26~28AWG	1
-1	U/M		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN LEON YEN 09NOV06	TE Connectivity														
DIMENSIONS: INCHES		CHK K. ZHU 09NOV06															
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD M WONG 09NOV06	NAME RJ45 TO RJ45														
<table border="1"> <tr><td>0 PLC</td><td>± 0.2</td></tr> <tr><td>1 PLC</td><td>± 0.1</td></tr> <tr><td>2 PLC</td><td>± 0.05</td></tr> <tr><td>3 PLC</td><td>± -</td></tr> <tr><td>4 PLC</td><td>± -</td></tr> <tr><td>ANGLES</td><td>± 2°</td></tr> </table>		0 PLC	± 0.2	1 PLC	± 0.1	2 PLC	± 0.05	3 PLC	± -	4 PLC	± -	ANGLES	± 2°	PRODUCT SPEC -	SIZE A3		
0 PLC	± 0.2																
1 PLC	± 0.1																
2 PLC	± 0.05																
3 PLC	± -																
4 PLC	± -																
ANGLES	± 2°																
MATERIAL -		FINISH -	APPLICATION SPEC -	CAGE CODE 00779	DRAWING NO C-1521822												
CUSTOMER DRAWING			WEIGHT 0.000000	RESTRICTED TO -													
			SCALE N.T.S	SHEET 1 OF 1	REV B1												