

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION





© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC U DIST -

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
0		REDRAWN WAS UTX DRW H2799	-	-	-



NOTES:

1. POST-FIT TYPE INSULATOR SUITABLE FOR USE ON THE FOLLOWING 6.3 QC RECEPTACLE P/NoS: 1627056, 1627057, 1627058, 1627059, & 1627194

NYLON 6/6 30% GF - BLACK	INSULATOR H2799	1-1659281-0
MATERIAL DESC.	DESCRIPTION	PART No.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: WR 5.3.03	Tyco Electronics Corporation AUSTRALIA				
ALL DIMENSIONS IN mm:		CHK: HT 5.3.03					
TOLERANCES UNLESS OTHERWISE SPECIFIED: DIMENSION (mm) TOLERANCE(+/-mm) LESS THAN 10 0.4 OVER 10 TO 30 0.5 OVER 30 TO 80 0.7 OVER 80 TO 250 1.0 ANGLES ±2°		APVD: PT 5.3.03	NAME: INSULATOR, POST-FIT				
		PRODUCT SPEC: -					
MATERIAL REF BLOCK	FINISH -	APPLICATION SPEC: -	WEIGHT: -	SIZE A3	CAGE CODE	DRAWING NO G-1659281	RESTRICTED TO -
CUSTOMER DRAWING			SCALE 1:1	SHEET 1	OF 1	REV 0	

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE OTHER THAN TYCO ELECTRONICS PERSONNEL WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA, USA.