




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
E4		REVISED PER ECR-23-188762	04JAN2024	PC	FDP

- 1 SPECIFICATIONS:  
MAGNET WIRE #18- #34 AWG  
1.02 mm(.040)- 0.16 mm(.006) DIA COPPER.
- 2 POCKET RECOMMENDATION: #1601431
- 3 TERMINAL APPLICATION TO COMPLY WITH TYCO ELECTRONICS SPECIFICATION 114-13166 FIGURE 10.
- 4 PRELIMINARY - NOT FOR PREPRODUCTION
- 5 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI.
- 6 TWO(2) TERMINALS SHOWN FOR ILLUSTRATION PURPOSES ONLY.
- 7 PREPRODUCTION-FASR REQUIRED.



	POST TIN OVER NICKEL	-	3-1601063-4
	POST TIN PLATE	-	1601063-4
	POST TIN PLATE	-	3-1601063-2
	POST TIN OVER NICKEL	-	4-1601063-3
	POST TIN OVER NICKEL	-	1601063-3
5	OBSOLETE PRE TIN PLATE	031-129-021	4-1601063-2
	POST TIN PLATE	131-130-021	2-1601063-2
	OBSOLETE PRE TIN PLATE	131-129-021	1601063-2

FINISH		REFERENCE PART NUMBER	TE PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.		TE Connectivity	
DWN J.WELLER 11JAN2002		STANDARD RANGE WIRE TO 1.50 X 0.81 TAB SIAMEZE TERMINAL	
CHK M.FEHER 11JAN2002		-	
APVD K.RANDOLPH 11JAN2002		-	
PRODUCT SPEC 108-2085		-	
APPLICATION SPEC		-	
MATERIAL BRASS, 3/4 HARD		WEIGHT 0.000000	RESTRICTED TO -
FINISH SEE TABLE		SCALE 6:1	SHEET 1 OF 1
		CUSTOMER DRAWING	REV E4