




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
0		CONVERTED RADIALL DWG TO TYCO ACAD DWG	11/03	—	—
1		REVISED	22APR10	RF	JM

- 1 FRONT AND REAR INSULATORS: THERMOSET EPOXY PER ASTM D 5948
 CONTACT RETENTION CLIPS: COPPER ALLOY PER ASTM B194
 REAR GROMMET: FLUOROSILICONE ELASTOMER PER MIL-R-25988B,
 EXCEPT 4.6.6.1
- 2 DATE CODE: YEAR & WEEK (YYWW)
- 3. DESCRIPTIVE PART NUMBER: GPRAE20SA
 THIS INSERT CONTAINS 20 CAVITIES FOR SIZE 22 SOCKET CONTACTS
- 4. THIS PRODUCT IS SOLD BY TYCO ELECTRONICS UNDER A LICENSE FROM RADIALL SA.



MATING FACE



THIS PRINT IS
PRELIMINARY
 UNQUALIFIED PRODUCT
 CONTACT PRODUCT ENGINEERING
 BEFORE USING THIS PRINT

1738083-1
 PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	NOV03	Tyco Electronics Corporation	
DIMENSIONS: mm [INCHES]		CHK	NOV03	Harrisburg, PA 17105-3608	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	NOV03	NAME	
0 PLC ± -		PRODUCT SPEC		GPR-A SOCKET INSERT, CLASS E, CONTACT ARRANGEMENT 20	
1 PLC ± -		APPLICATION SPEC		SIZE	RESTRICTED TO
2 PLC ± 0.05 [.002]				A2	—
3 PLC ± -				CAGE CODE	
4 PLC ± -				00779	
ANGLES ± -				DRAWING NO	
FINISH				C=1738083	
MATERIAL		WEIGHT		SCALE	
1				1:1	
		CUSTOMER DRAWING		SHEET	
				1 OF 1	
				REV	
				1	