







Material:
Housing: glassfilled polyester, colour gray
Actuator: glassfilled polyester, colour red
Contacts: phosphor-bronze, min. 2,5 µm. tin

For p.c. board thickness 2,4 mm.
Recommended hole size 0,8 mm.

- 1 Switch housings have profile A, B or C
- 2 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI


DO NOT SCALE

DIMENSIONS IN mm



METRIC

THIRD ANGLE
PROJECTION



REVISIONS

LTR	DISCRIPTION	DATE	DWN	APVD
L1	REVISED PER ECO-09-022178	13AUG09	KK	AEG

	partnumber	number of positions	"L"
OBSOLETE	161391 - 1	1	5,08
	- 2	2	7,62
	- 3	3	10,16
	- 4	4	12,70
OBSOLETE	- 5	5	15,24
	- 6	6	17,78
	- 7	7	20,32
	- 8	8	22,86
OBSOLETE	- 9	9	25,40
	1- - 0	10	27,94
	1- - 1	11	30,48
	1- - 2	12	33,02
	1- - 3	13	35,56
	1- - 4	14	38,10
	1- - 5	15	40,64
	1- - 6	16	43,18
	1- - 7	17	45,72
	1- - 8	18	48,26
	1- - 9	19	50,80
	2- - 0	20	53,34
	2- - 1	21	55,88
	2- - 2	22	58,42
	2- - 3	23	60,96
	2- - 4	24	63,50
	2- - 5	25	66,04
	2- - 6	26	68,58
	2- - 7	27	71,12
	2- - 8	28	73,66
	2- - 9	29	76,20
	3- - 0	30	78,84

FINISH MATERIAL PART NUMBER

CUSTOMER
DRAWING

AMP

AMP-HOLLAND B.V.
's-Hertogenbosch, The Netherlands

FOR REFERENCE ONLY
WILL NOT BE UPDATED

THIS DRAWING IS UNPUBLISHED RELEASED FOR PUBLICATION 19
© COPYRIGHT 1980 BY AMP-HOLLAND B.V.
ALL INTERNATIONAL RIGHTS RESERVED.
AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

DR. PVT JAN '84

WIRE RANGE

NAME TINPLATED DIP SWITCH
SOLDERLEGLNGTH 4,0 MM.

REV. DATE
D M Y

CHK.

INSUL. RANGE

07 10 09

APP.

SIZE
A3

SHEET
OF

DRAWING NO
C-161391

REV. LTR.
L1