


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL INTERNATIONAL RIGHTS RESERVED.




LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN	APVD	
DF	00	0	CONVERTED RADIALL DWG TO TYCO ACAD DWG	11/03	--	--
		1	REVISED	22APR10	RF	JM

- 1 FRONT & REAR INSULATORS: THERMOSET EPOXY PER ASTM D5948
 CONTACT RETENTION CLIPS: COPPER ALLOY PER ASTM B194
 REAR GROMMET & INTERFACIAL SEAL: FLUOROSILICONE ELASTOMER PER MIL-R-25988 B, EXCEPT 4.6.6.1

- 2 DATE CODE: YEAR & WEEK (YY WW)
- 3. DESCRIPTIVE PART NUMBER: GPRBE34PB
 THIS INSERT CONTAINS:
 16 CAVITIES FOR SIZE 20 PIN CONTACTS
 18 CAVITIES FOR SIZE 22 PIN CONTACTS
- 4. THIS PRODUCT IS SOLD BY TYCO ELECTRONICS
 UNDER A LICENSE FROM RADIALL SA.



MATING FACE



THIS PRINT IS
PRELIMINARY
 UNQUALIFIED PRODUCT
 CONTACT PRODUCT ENGINEERING
 BEFORE USING THIS PRINT

1738181-1
 PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R FLAIG NOV03	Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]		CHK J MOSIER NOV03	NAME GPR-B PIN INSERT	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J MOSIER NOV03	CLASS E	
0 PLC ± -		PRODUCT SPEC	CONTACT ARRANGEMENT 34 KEY B	
1 PLC ± -		APPLICATION SPEC	SIZE A2	RESTRICTED TO
2 PLC ± 0.05 [.002]		WEIGHT -	CAGE CODE 00779	DRAWING NO C=1738181
3 PLC ± -		MATERIAL -	SCALE 1:1	SHEET 1 OF 1
4 PLC ± -		FINISH -	REV 1	
ANGLES ± -		CUSTOMER DRAWING		