


REV.	DATE	DESCRIPTION
E	91/02/27	21317 REDRAWN, ADD NOTE TO MFG. HOLES
F	95/11/09	29130 QTY'S CORRECTED ON FIND NOS 1,4,5,6, & 8. *NC* ADDED TO CONFIGURATION



HERMETICALLY SEALED

CONSTRUCTION
 MAIN CONTACTS
 CONFIGURATION
 VOLTAGE (NOMINAL)
 CURRENT: RES.
 COIL DATA
 DUTY CYCLE
 NOM. COIL VOLTAGE
 TRIP MAX.
 RESET MAX.
 AMBIENT TEMP.
 ENVIRONMENTAL DATA
 ALTITUDE
 LIFE: ELECTRICAL
 MECHANICAL
 WEIGHT, MAX. (EST)

1 NO-1 NC MAGN. LATCH
 3 VDC
 25 AMP
 INTERMITTENT
 28 VDC
 18 VDC
 16 VDC
 -55°C TO +71°C
 50,000 FEET MAX.
 50,000 CYCLES MIN.
 100,000 CYCLES MIN.
 7.5 OZ.



OPPOSITE 2 MOUNTING HOLES
 TO BE FREE OF PAINT
 LOCATION OPTIONAL



QTY	PART OR IDENTIFYING NO	DESCRIPTION	QTY	DESCRIPTION	QTY	DESCRIPTION
1	51808-064	WASHER-LOCK NO. 8 SPLIT	1	ANG35B8	1	BRONZE
4	51806-014	WASHER-LOCK NO. 6 SPLIT	4	ANG35B6	4	BRONZE
2	51805-021	WASHER-LOCK NO. 5 INT.	2		2	BRONZE
4	50408-034	NUT-8-32 X 5/16 X 3/32 HEX.	4		4	BRASS
4	50406-034	NUT-6-32 X 1/4 X 5/64 HEX.	4		4	BRASS
1	33374-010	RELAY ASSEMBLY-PRIMARY	1		1	
1	32135-001	PLATE-WIRING DIAGRAM	1		1	
2	30943-001	SCHEM-NYLON 5-40	2		2	
1	16728-008	PLATE-BASE COVER	1		1	
1	16043-001	PLATE-NAME	1		1	
2	7517-002	WASHER-BASE SPACER	2		2	

HARTMAN ELECTRICAL MANUFACTURING
 MANUFACTURED IN OHIO

RELAY-INO, INC
 25 AMPS MAGNETIC LATCHING
 093

DR BY	RS	195/11/16
CHK BY	RS	195/11/16
ENGR	RS	195/11/16
MFG	RS	195/11/16
RELEASE		
CONTR. NO.		
GOVT APPVAL		

SIZE C
 CODE IDENT DWG NO. 74063
 SCALE NONE
 SHEET