

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC

DIST

J

—

REVISIONS

変更

DESCRIPTION

DATE

DWN

APVD

P

LTR

B

ECR-12-009867

6NOV12

SY

AC

4,6 MIN.

15.7 MIN.

f

4,6 MIN.

5,9

1.3^{+0.10}_{-0.15}

2

4,0

11X4,0=44,0

49.9 ± 0.10

24

2.95^{+0.05}_{-0.13}

ACTION PIN AREA

CONTACT AREA

11x 4,0 = 44,0

4,0

25

1

2,0

4,0

4x 2,0 = 8,0

1,5

24x 2,0 = 48,0

0,05

ALL HOLES

EDGE OF P.C.BOARD

3

4

P.C.B. HOLE DIM. ACTION PIN

FIN. HOLE : 0,55 TO 0,65 mm

OTHER REQUIREMENTS: SEE APPLICATION SPECIFICATION 114-19029

COMPONENT SIDE AS SHOWN

RECOMMENDED PCB-HOLE LAY-OUT

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: 単位: 桁 mm

TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差 ±0.3

0-PLC ±

1-PLC ±

2-PLC ±

3-PLC ±

4-PLC ±

ANGLES ± 3°

MATERIAL 材料

FINISH 仕上

DWN T.KATANO 31MAY04

CHK T.KIMURA 31MAY04

APVD K.IKEGAMI 31MAY04

PRODUCT SPEC 製品規格 108-19082

APPLICATION SPEC 取付適用規格 114-19029

WEIGHT -

CUSTOMER DRAWING

Tyco Electronics

Tyco Electronics AMP K.K.

Kawasaki, Japan

NAME 名称

Z-PACK 2mm HM

GROUND RETURN LOWER SHIELD

TYPE B 25 COLUMNS

SIZE A2

CAGE CODE 00779

DRAWING NO 番号 C=1746986

RESTRICTED TO -

SCALE 尺度 5:1

SHEET 1 OF 1

REV B

△ PLATING:

CONTACT AREA: 0,76 μm Au MIN. OVER 1,27 μm Ni MIN.

ACTION PIN : 0,5 μm SnPb MIN. (NO CONVERSION TO LEADFREE)

REMAINDER : Ni

△ MATERIAL; PHOSPHORBRONZE.

△ ROW "f" 12 PLATED THROUGH HOLES FOR LOWERSHIELD.

△ HOLE PATTERN FOR FEMALE CONNECTOR TYPE B-25 COLUMNS WITH

UPPERSHIELD, 125+13 PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID.

5 MAX. BOARD THICKNESS 3,5 mm.

△ PLATING:

CONTACT AREA: 0,76 μm Au MIN. OVER 1,27 μm Ni MIN.

ACTION PIN : 0,5 μm Sn MIN.

REMAINDER : Ni

△ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

△ 1746986

AMP 1471-9 REV 31MAR2000
R6-129
(REV.04-91)

1746986