




LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	APVD
J	—	A		ECR-12-007088	17APR12	SY AC
		B		ECR-12-009867	6NOV12	SY AC

- 1 PLATING CONNECTOR:
CONTACT AREA: 0,76μm Au MIN. OVER 1,27μm Ni MIN.
ACTION PIN : 0,5μm SnPb MIN. OVER 1,27μm Ni MIN.
- 2 PLATING CONNECTOR:
CONTACT AREA: 0,76μm Au MIN. OVER 1,27μm Ni MIN.
ACTION PIN : 0,5μm Sn MIN. OVER 1,27μm Ni MIN.
- 3 PLATING SHIELD:
CONTACT AREA: 0,76μm Au MIN.
ACTION PIN : 0,5μm SnPb MIN.
REMAINDER : Ni
- 4 PLATING SHIELD:
CONTACT AREA: 0,76μm Au MIN.
ACTION PIN : 0,5μm Sn MIN.
REMAINDER : Ni
- 5 MATERIAL CONTACTS; PHOSPHORBRONZE
MATERIAL SHIELD; PHOSPHORBRONZE
MATERIAL HOUSING; GLASSFILLED POLYESTER (GRAY)
- 6 ASSEMBLY PRINTED WITH P/N AND DATECODE
THE MARKING CAN APPEAR ON THE FRONT SIDE OR BACK SIDE.
- 7 HOLE PATTERN FOR FEMALE CONNECTOR TYPE B
125 PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID
- 8 ROW "f" 13 PLATED THROUGH HOLES FOR UPPERSHIELD
CONNECTOR LUBRICATED WITH BELLCORE
APPROVED LUBRICANT, TECHNICAL REFERENCE
TR-NWT-001217 ISSUE 1, SEPT. 1992.
CONNECTOR TESTED AND QUALIFIED AGAINST BELLCORE
QUALITY LEVEL III, CENTRAL OFFICE APPLICATIONS.
- 9

10 BASIC P.N. LOWERSHIELD: 1746986.

11 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING
PER D.RENAUD/D.SINISI

11 OBSOLETE	2 4 9	3	1-1746993-9
	2 4	3	1-1746993-1
11 OBSOLETE	1 3 9	3	-1746993-9-
11 OBSOLETE	1 3	3	-1746993-1-
FINISH		MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T.KATANO 10MAY04	Tyco Electronics AMP K.K. Kawasaki, Japan	
DIMENSIONS: 単位: 桁 mm		CHK T.KIMURA 14MAY04	NAME 名称	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差		APVD K.IKEGAMI 14MAY04	Z-PACK 2mm HM 125 POS. FEMALE CONNECTOR TYPE B WITH GROUND RETURN UPPER SHIELD	
0 PLC ± 0.3 1 PLC ± 0.3 2 PLC ± 0.3 3 PLC ± 0.3 4 PLC ± 0.3 ANGLES ± 3°		PRODUCT SPEC 製品規格 108-19082	SIZE A2	
MATERIAL 材料 SEE TABLE		APPLICATION SPEC 取付適用規格 114-19029	CAGE CODE 00779	
FINISH 仕上 SEE TABLE		WEIGHT —	DRAWING NO 番号 C=1746993	
CUSTOMER DRAWING		SCALE 尺度 5:1	SHEET 1 OF 1	
			REV B	