





THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION
© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.		
DESCRIPTION	MATERIAL	FINISH
MODULE ASSEMBLY	THERMOSET EPOXY	COLOR: BLACK
GROMMET	FLUORSILICONE RUBBER	COLOR: BLUE
CONTACT SOCKET	BERYLLIUM COPPER PER QQ-C-533	GOLD PLATE PER MIL-G-45204
RETAINING CLIP	BERYLLIUM COPPER PER QQ-C-533 OR STAINLESS STEEL PER QQ-S-766	NONE
DIODES (QTY=4)	JANTX1N5618	- -

LDC	DIST	REVISIONS					
DF	AO	P	LTR	DESCRIPTION	DATE	DWN	APVD
		A		REV PER ECD 08-000580	15JAN2009	PK	DE



SCHEMATIC DIAGRAM



1 MARK MODULE ASSEMBLY WITH "AMP", AMP PART NO. AND DATE CODE .060 MINIMUM HIGH CHARACTERS AT APPROXIMATE AREA SHOWN.

2. PIN CONTACTS, SEALING PLUGS AND TOOLS NOT SUPPLIED MUST BE ORDERED SEPARATELY.

ITEMS	AMP P/N	MILITARY P/N
PIN CONTACTS	2-592404-1	M39029/1-101
SEALING PLUGS	592104-1	MS27488-20
TOOLS	592105-1	M81969/14-11

3. MODULE MEETS APPLICABLE REQUIREMENTS OF MIL-T-81714 CLASS "B". ENVIRONMENTS CREATED BY OPERATION OF INTERNAL ELECTRIC COMPONENTS WHICH EXCEED THE MODULE RATED PERFORMANCE IS THE RESPONSIBILITY OF THE USER. THE ELECTRONIC COMPONENT SPECIFICATION SHOULD BE CONSULTED.

FAR SIDE

1757212-1  
PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	6-21-04	Tyco Electronics Corporation Harrisburg, PA 17105			
		CHK	6-21-04				
		APVD	6-21-04				
		PRODUCT SPEC					
DIMENSIONS INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
	0 PLC ± -	D. EABY		A2	00779	C=1757212	-
	1 PLC ± -	D. EABY		SCALE 2:1 SHEET 1 OF 1 REV A			
	2 PLC ± -	APPLICATION SPEC		CUSTOMER DRAWING			
	3 PLC ± .010						
	4 PLC ± -						
	ANGLES ± -						
MATERIAL	FINISH	WEIGHT					
SEE TABLE	SEE TABLE	-					