

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL INTERNATIONAL RIGHTS RESERVED.


LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
DF	00				
	0	CONVERTED RADIALL BORDER TO TYCO ACAD BORDER	11/03	—	—
	1	REVISED	22APR10	RF	JM

1 FRONT & REAR INSULATORS: THERMOSET EPOXY PER ASTM D5948
 CONTACT RETENTION CLIPS: COPPER ALLOY PER ASTM B194

2 DATE CODE: YEAR & WEEK (YY WW)



3. DESCRIPTIVE PART NUMBER: GPRBN34SB
 THIS INSERT CONTAINS:
 18 CAVITIES FOR SIZE 22 SOCKET CONTACTS
 16 CAVITIES FOR SIZE 20 SOCKET CONTACTS

4. THIS PRODUCT IS SOLD BY TYCO ELECTRONICS
 UNDER A LICENSE FROM RADIALL SA.




MATING FACE

27.0 [1.063] / 26.96 [1.061]



12.05 [.474] / 12.01 [.473]



THIS PRINT IS
PRELIMINARY
 UNQUALIFIED PRODUCT
 CONTACT PRODUCT ENGINEERING
 BEFORE USING THIS PRINT

1738185-1
 PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	NOV03	Tyco Electronics Corporation	
		CHK	NOV03	Harrisburg, PA 17105-3608	
		APVD	NOV03	NAME	
		PRODUCT SPEC		GPR-B SOCKET INSERT	
		APPLICATION SPEC		CLASS N	
		WEIGHT		CONTACT ARRANGEMENT 34 KEY B	
		CUSTOMER DRAWING		SIZE	RESTRICTED TO
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CAGE CODE	DRAWING NO
0 PLC ± -		1 PLC ± -		A2	00779
2 PLC ± 0.05 [.002]		3 PLC ± -		C=	1738185
3 PLC ± -		4 PLC ± -		SCALE	1:1
4 PLC ± -		ANGLES ± -		SHEET	1 of 1
MATERIAL		FINISH		REV	1
-		-			