

NUMBER C-176359

3rd ANGLE PROJECTION


METRIC

Proj. 399-211

DIMENSIONS IN MILLIMETERS. DO NOT SCALE PRINT


PRINT DIST

-1:AS SHOWN




NOTES


- △ FINISH;
- 0.0013MIN. NICKEL UNDER PLATING
- 0.00076MIN. GOLD PLATING IN ZONE I
- 0.0005-0.0035 TIN-LEAD PLATING IN ZONE II
- 2 RECOMMENDED THRU HOLE SPEC.;
- BOARD THK.: 2.2±0.2
- DRILLED HOLE DIA.: 0.9±0.025
- FINISHED HOLE DIA.: 0.825±0.05
- CU PLATING THK.: 0.025-0.05




SECT. "A-A", "C-C"
(SCALE 20-1)




SECT. "B-B"
(SCALE 20-1)



DETAIL "D"
(SCALE 20-1)



DETAIL "E"
(SCALE 20-1)



DETAIL "F"
(SCALE 20-1)

				© 1990 BY AMP (Japan) LTD. ALL RIGHTS RESERVED.				AMP AMP (JAPAN) LTD. Tokyo, Japan			
				WIRE RANGE --- 0.5mm CANS ---				INSULATION DIA ---			
				MATERIAL COPPER ALLOY				FINISH SEE NOTE △			
O RELEASED				DR. T. SASAKI 3/13/90				DE. T. SASAKI 3/13/90			
LTR				CHK. T. SASAKI 3/13/90				APP. [Signature] 3/13/90			
REVISION RECORD				DR				GENERAL TOLERANCE			
				DATE				0<L<10 : ±0.2			
								10<L<30 : ±0.25			
								30<L<100 : ±0.3			
								ANGLES : ±3°			
								NAME			
								FEED-THRU POST ACTION PIN			
								GENERAL TOLERANCE			
								SIZE LOC NUMBER			
								A3 J C-176359			
								SCALE			
								REV. 0			
								SHEET 1 OF 1			

CUSTOMER DRAWING