




REVISIONS

P	LTR REV	DESCRIPTION MODIFICATIONS	DATE	DWN DESS.	APVD APP.
	A	CREATION	12JAN2005	TR	GJ
	B	MODIF CHEMINEES DERIVES	01FEVR2005	TR	GJ
	C	MODIF LONGUEUR VIS, AJOUT RONDELLES	31MAR2008	TR	AG
	D	ECR-19-003429, ADD 2 O'RINGS	04MAR2019	BM	NA



SCALE 1:2

CAPACITIES MINI/MAXI (mm2)

MAIN CONDUCTOR		TAP CONDUCTOR	
Sector Stranded	Sector solid	Sector Stranded Round Stranded	Sector Solid Round Solid
70 / 120	95 / 150	6 / 50	- / 70

TCPN

PRODUCT DESC

F 34646-000

HEL-6875-2X

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
TOLERANCES NON SPECIFIEES: -

FINISH
FINITION -

DIMENSIONS:

mm

DWN/DESSINE
T. ROUSSEAU

12JAN2005

MATERIAL
MATIERE -

CHK/VERIFIE
A. GUICHARD

APVD/APPROUVE
N. ALMEIDA

PRODUCT SPEC
SPEC. PRODUIT -

APPLICATION SPEC
SPEC. APPLICATION -

WEIGHT
MASSE APPROX.

458g

NAME
TITRE

RING CONNECTOR
HEL-6875-2X

SIZE
FORMAT
A 4

CAGE CODE
00779

DRAWING NO
No. PLAN

C-1830094

RESTRICTED TO
RESERVE A

CUSTOMER DRAWING

/PLAN CLIENT

UNIQUEMENT
POUR REFERENCE

SCALE
ECHELLE 1:1

SHEET
FEUILLE

OF
DE 1

REV
D

20

RELEASED FOR PUBLICATION
LIBRE A LA DIFFUSION

ALL RIGHTS RESERVED.
TOUS DROITS RESERVES.

THIS DRAWING IS UNPUBLISHED.
DIFFUSION RESTREINTE

BY -

COPYRIGHT 20

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
TOLERANCES NON SPECIFIEES
(SUIV NB DE DECIMALES):

0 PLC/DEC: ±0
1 PLC/DEC: ±0
2 PLC/DEC: ±0
3 PLC/DEC: ±0
4 PLC/DEC: ±0

ANGLES ±

