



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
		C2	REL PER ECR-12-002492	06FEB2012	Q.L LP



1820026-2	C39195-Z7702-A10	1000 ⁺⁰ ₋₄₀
1820026-1	C39195-Z7702-A20	2000 ⁺⁰ ₋₄₀
TE P/N	CUSTOMER P/N	LENGTH

PIN ASSIGNMENT :



- NOTE:
- ELECTRICAL TEST:
 CONTINUITY RESISTANCE: =<1 Ohms.
 INSULATION RESISTANCE: >=50 MOhms.
 HI-POT: DC300V/0.01Sec
 - DIRECTIVE 2002/95/EC COMPLIANT
 - FLAME RATE 94V-0 IS INDICATED IN CONNECTOR
 - VOLTAGE RATING RATED 30V
 - LABEL, REF SPECIFICATION 118-19330

1PC39195-Z7702-A20

BARCODE

WK EE/YY 2.0M ET
 0-1820026-1 rev.*
 C39195-Z7702-A20
 TE

1820026-1

C39195-Z7702-A10

BARCODE

WK EE/YY 1.0M ET
 0-1820026-2 rev.*
 C39195-Z7702-A10
 TE

1820026-2

AR	KG	PE	ITEM
1	MR	LABEL, 44*44MM	9
AR	MR	COPPER FOIL, W=15MM, ONLY ELECTRIC.	8
AR	MR	COPPER FOIL, W=6MM, BOTH ELECTRIC.	7
AR	MR	COPPER FOIL, W=20MM, ONLY ELECTRIC.	6
1	PC	FERRITE CORE,T5B,OD:14.27MM,L:28.5MM,ID:6.35MM.	5
AR	MR	USB 2.0 CABLE, 28AWGx1P+24AWGx2C+AL/MYLAR +DRAIN+BRAID. COLOR: WHITE(WH01).	4
AR	KG	OVERMOLD PVC, 40P, WHITE(WH01).	3
1	PC	USB B TYPE, MALE, CONTACTS: GOLD PLATED 30u", SHELL: NICKEL PLATED, INSULATION: WHITE.	2
1	PC	USB A TYPE, MALE, CONTACTS: GOLD PLATED 30u", SHELL: NICKEL PLATED, INSULATION: WHITE.	1
QTY	U/M	DESCRIPTION	ITEM

6. CABLE ASSEMBLY IS COMPLIANT WITH USB2.0 STANDARDS

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SUNNY TSAI 28SEP04		STE TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:			
		0 PLC	± -	USB/A TO USB/B CABLE ASSEMBLY	
		1 PLC	± -		
MATERIAL		FINISH		APVD - NAME PRODUCT SPEC - APPLICATION SPEC - SIZE CAGE CODE DRAWING NO RESTRICTED TO A3 00779 C-1820026 -	
-		-		WEIGHT - CUSTOMER DRAWING SCALE N.T.S SHEET 1 OF 1 REV C2	