



LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD		
H	-	C	ECR-11-004693	01APR2011	RC	AH	



FIBER CONNECTIVITY	
LEFT PLUG	RIGHT PLUG
PIN 1	PIN 2
PIN 2	PIN 1



STANDARD LENGTHS ACCORDING TO CUSTOMER DRAWING 1920950	
PART NUMBER	"L" (meter) <sup>3</sup>
X-1920933-Y	XY.0
8-1920933-1	1.2

- NOTES:
- REFER TO TE CONNECTIVITY CUSTOMER DRAWING 2064160 FOR CABLE ASSEMBLY LOSS AND WAVELENGTHS THAT CABLE ASSEMBLY LOSS WILL BE TESTED TO
  - MINIMUM RETURN LOSS: 45 dB FOR ODC PLUG  
RETURN LOSS WILL BE TESTED AT 1310 nm AND 1550 nm WAVELENGTHS
  - STANDARD LENGTHS AND LENGTH TOLERANCE ACC. TO TE CONNECTIVITY CUSTOMER DRAWING 1920950
  - INFORMATION ON LABEL SEE DETAIL:
    - BARCODE
    - UNIQUE SERIAL NUMBER
    - ASSEMBLY LENGTH
    - TE CONNECTIVITY PART NUMBER
    - TE CONNECTIVITY ORDER NUMBER
  - ALLOWABLE TORQUE: 1 Nm TO 2 Nm WHEN TIGHTENING PLUG NUT

1	FOAC INFORMATION LABEL	4
2	FOAC ODC CAP PLUG PLASTIC NO CHAIN	3
2	FOKIT ODC PLUG ASSEMBLY, 2 FIBER, SINGLE MODE	2
L	FOCAB ODC 5.5 mm 2FOLD, SINGLE MODE 9/125, BLACK	1
Qty	Description	Item

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. COOLEN 20MAY2008														
DIMENSIONS: METERS		CHK A. HENGELMOLEN 20MAY2008														
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD A. HENGELMOLEN 20MAY2008	NAME FIBER OPTIC ODC LEAD 2 FOLD PLUG - 2 FOLD PLUG SINGLE MODE 9/125													
<table border="1"> <tr><td>0 PLC</td><td>± -</td></tr> <tr><td>1 PLC</td><td>± -</td></tr> <tr><td>2 PLC</td><td>± -</td></tr> <tr><td>3 PLC</td><td>± -</td></tr> <tr><td>4 PLC</td><td>± -</td></tr> <tr><td>ANGLES</td><td>± -</td></tr> </table>		0 PLC	± -	1 PLC	± -	2 PLC	± -	3 PLC	± -	4 PLC	± -	ANGLES	± -	PRODUCT SPEC -	SIZE A2	CAGE CODE 00779
0 PLC	± -															
1 PLC	± -															
2 PLC	± -															
3 PLC	± -															
4 PLC	± -															
ANGLES	± -															
MATERIAL -		FINISH -	WEIGHT -	DRAWING NO C=1920933												
CUSTOMER DRAWING			SCALE NTS	SHEET 1 of 1												

1920933