





REVISIONS				
P	LTN	DESCRIPTION	DATE	APVD
A		REL PER ECO-10-005637	23MAR2010	WS RP
B		REVISED PER ECO-19-012987	30AUG2019	AP SY



- 1 MATERIAL:  
CONTACT - PHOS BRONZE  
HOUSING - LCP, UL 94V-0, COLOR - BLACK
- 2 FINISH:  
CONFORMS TO THE REQUIREMENTS OF  
TE PRODUCT SPECIFICATION 108-2303-1; BASED  
ON TELECORDIA GR-1217-CORE FOR SYSTEM  
QUALITY LEVEL III, APPLICATIONS IN  
CONTROLLED ENVIRONMENTS (CENTRAL OFFICE).
- 3 CONNECTOR MARKED WITH PART NUMBER, DATE CODE,  
85 OHM, AND STANDARD IN APPROXIMATE AREA SHOWN.
- 4 DATUMS AND BASIC DIMENSIONS ESTABLISHED BY  
CUSTOMER.
- 5 CONTACT AREA LUBRICATED WITH BELLCORE  
APPROVED LUBRICANT, TECHNICAL REFERENCE  
GR-1217-CORE, ISSUE 1, NOVEMBER 1995.
- 6 REFERENCE APPLICATION SPEC FOR RECOMMENDED PLATED THRU  
HOLE DIAMETER AND PLATING THICKNESS.
- 7 SHOWN LOGO OR OTHER TE OWNED LOGOS IN APPROXIMATE AREA



RECOMMENDED PC BOARD  
LAYOUT BACKPLANE,  
COMPONENT SIDE SHOWN  
SCALE 6:1

1934937-1  
PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.K. SHOBER 27MAY2008 CHK C. RITIER 27MAY2008 APVD C. RITIER 27MAY2008	TE Connectivity
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±	NAME HEADER ASSEMBLY, OPEN ENDED, 5 PAIR, 10 COLUMN TinMan 85 OHM	
MATERIAL FINISH	WEIGHT RESTRICTED CUSTOMER	PRODUCT SPEC 108-2303-1 APPLICATION SPEC 114-13243	SIZE CAGE CODE DRAWING NO A 100779 C=1934937
		SCALE 10:1	SHEET 1 OF 1 REV B