


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
J	-		1	PROPOSED	27NOV08	TA	HY



1. APPLICABLE WIRE RANGE:
 CAN 0.22mm²
 2. APPLICATOR FEED: 7.5mm
1. 適用電線: CAN 0.22mm²
 2. アプリケータ送りピッチ: 7.5mm

PRELIMINARY
 THIS ITEM HAS POSSIBILITY OF DESIGN CHANGE WITHOUT NOTIFICATION.

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS: 単位: 概 mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差 ±0.3 0-PLC ± 1-PLC ±0.5 2-PLC ±0.13 3-PLC ±0.013 4-PLC ±0.001 ANGLES ±3'00"	DWN T. AKIGUCHI 27NOV08 CHK R. KOMIYAMA 27NOV08 APVD H. YAMAGAMI 27NOV08
MATERIAL 材料 Cu Alloy	FINISH 仕上 PRE-TIN	PRODUCT SPEC 108-78518 APPLICATION SPEC 取付適用規格 114-5400

WIRE RANGE 包合電線断面積 0.22mm ²	INSULATION DIA 被覆外径 φ1.4~φ1.5	Tyco Electronics Corporation Kawasaki, Japan	
NAME 名称 SEALED 0.50 RECEPTACLE CONTACT Sn S-SIZE		SIZE A3	CAGE CODE 00779
DRAWING NO 番号 C=1981878		RESTRICTED TO -	
CUSTOMER DRAWING		SCALE 尺度 5.1	SHEET OF REV