




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	F1	REVISED PER ECR-24-226845	24DEC2024	C.X	L.C


(2 POS.)



CIRCUIT NO.1 MARK





SEC. B-B




SEC. D-D

NOTE:
1. GENERAL TOLERANCE: ± 0.3 , $\pm 3^\circ$
2. MATERIAL: 66NYLON GF(UL94V-0)
3. MATING CONN. P/N: SEE TABLE
4. APPLICABLE CONTACT P/N:
1971031-1




TRADE MARK




(2 POS.)

TRADE MARK




(3~4 POS.)

TRADE MARK




(5 POS.)

TRADE MARK



(6~8 POS.)


TRADE MARK




(9~10 POS.)

KEY TYPE NO.

PITCH 2.0



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Liu Jimmy 11JUN2008	TE Connectivity Ltd.		
DIMENSIONS: mm		CHK Wu happy 11JUN2008			
		APVD Zhou Julian 11JUN2008	NAME		
		PRODUCT SPEC 108-106001	Grace Inertia Connector 2.0 EV Series Plug Housing		
MATERIAL SEE NOTE		APPLICATION SPEC 114-5425	SIZE A2	CAGE CODE 00779	DRAWING NO C=1971030
		WEIGHT 0	RESTRICTED TO -		
		CUSTOMER DRAWING	SCALE N/A	SHEET 1 OF 4	REV F1



4

3


2

1


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-











(8 POS.)



(9 POS.)



(10 POS.)



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
-

FINISH
-

TOLERANCES, UNLESS OTHERWISE SPECIFIED

0 PLC	±	-
1 PLC	±	-
2 PLC	±	-
3 PLC	±	-
4 PLC	±	-
ANGLES	±	-

FINISH
-

DWN
Liu Jimmy
11JUN2008

CHK
Wu Hapye
11JUN2008

APVD
Zhou Julian
11JUN2008

PRODUCT SPEC
108-106001

APPLICATION SPEC
114-5425

WEIGHT
-

CUSTOMER DRAWING

 TE Connectivity Ltd.

NAME
Grace Inertia Connector 2.0 EV Series
Plug Housing

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=1971030

RESTRICTED TO
-

4

3

2



1

REVISIONS



P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

2P~6P KEY TYPE



KEY A





KEYB





KEY E



KEY C





KEY D





7P~10P KEY TYPE



KEY A





KEYB



KEY C





KEY D





5P KEY TYPE



KEY F



KEY G



KEY H



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES, UNLESS OTHERWISE SPECIFIED

0 PLC	±	-
1 PLC	±	-
2 PLC	±	-
3 PLC	±	-
4 PLC	±	-
ANGLES	±	-
FINISH	-	-

DWN
Liu Jimmy
11JUN2008

CHK
Wu Sam
11JUN2008

APVD
Zhou Julian
11JUN2008

PRODUCT SPEC
108-106001

APPLICATION SPEC
114-5425

WEIGHT
-

CUSTOMER DRAWING

TE Connectivity Ltd.

NAME
Grace Inertia Connector 2.0 EV Series Plug Housing

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=1971030

RESTRICTED TO
-

SCALE
N/A

SHEET
4 OF 4

REV
F1

1471-9 (1/15)