








P		LTR	DESCRIPTION	DATE	DWN	APVD
	D2	REVISION TABEL UPDATE		26SEP2024	AR	VP



	32	8.33 [.328]	7.37 [.290]	13.21 [.520]	17.78 [.700]	10.16 [.400]	4	5	1977162-5
△ ₆	72	23.58 [.928]	22.62 [.890]	43.72 [1.720]	48.30 [1.900]	40.67 [1.600]	16	17	1977162-4
△ ₆	72	21.04 [.828]	20.08 [.790]	38.64 [1.520]	43.21 [1.700]	13.59 [1.400]	14	15	1977162-3
△ ₆	56	18.51 [.728]	17.53 [.690]	33.55 [1.320]	38.13 [1.500]	30.50 [1.200]	12	13	1977162-2
	44	9.60 [.378]	8.64 [.340]	15.76 [.620]	16.26 [.800]	12.70 [.500]	5	6	1977162-1
	EIA 481 TAPE WIDTH mm	F	E	D	C	B	A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 12JUL2007 R BROWN CHK 12JUL2007 R BROWN APVD 12JUL2007 R BROWN		 TE Connectivity Ltd.	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.13 [.005] 4 PLC ± - ANGLES ± - FINISH		NAME HEADER ASSEMBLY, LATCHING, RIGHT ANGLE SURFACE MOUNT, MTE, AMPMODU	
		PRODUCT SPEC 108-25034 APPLICATION SPEC -		SIZE A1	
MATERIAL 		WEIGHT -		CAGE CODE 00779	
		CUSTOMER DRAWING		DRAWING NO 1977162	
				SCALE 6:1	
				SHEET 1 of 2	
				REV D2	



RECOMMENDED PC BOARD LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm (INCHES)

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0. PLC	± .
1. PLC	± .
2. PLC	± .
3. PLC	± 0.13 [.005]
4. PLC	± . ± .
ANGLES	

FINISH

DWN
R BROWN
12JUL2007

CHK
R BROWN
12JUL2007

APVD
R BROWN
12JUL2007

NAME

108-25034

APPLICATION SPEC

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

WEIGHT

A100779

1977162

CUSTOMER DRAWING

SCALE 6:1

SHEET 2 OF 2

REV D2

TE Connectivity Ltd.