






4 3 2 1

CONVERSION CHART	
INCH	MM
.004	0.10
.009	0.23
.010	0.25
.019	0.48
.031	0.79
.035	0.90
.055	1.40
.067	1.70
.100	2.54
.125	3.18
.140	3.56
.197	5.00
.200	5.08
.267	6.78
.298	7.57
.400	10.16
.498	12.65
.600	15.24
.698	17.73
.800	20.32
.898	22.81
1.000	25.40
1.098	27.89



RECOMMENDED HOLE LAYOUT
TOLERANCE ±.002 UNLESS OTHERWISE NOTED



CIRCUIT DIAGRAM

△ SPECIFICATIONS:

△△B
△3

MATERIAL:
 BASE: PPS, UL RATED 94V-0. (BLACK)
 COVER: POLYESTER, UL RATED 94V-0. (BLACK)
 ACTUATOR: POLYAMIDE, UL RATED 94V-0. (WHITE)
 MOVING CONTACT: COPPER ALLOY, GOLD FLASHED.
 FIXED CONTACT: COPPER ALLOY, TIN LEAD PLATED.
 TERMINALS: COPPER ALLOY, TIN LEAD PLATED.

ELECTRICAL:
 CONTACT RATING: 0.4 VA MAX. @ 20 VDC.
 INITIAL CONTACT RESISTANCE: 50 MILLIOHMS MAX.
 INSULATION RESISTANCE: 100 MEGOHMS MIN. AT 100 VDC.
 DIELECTRIC STRENGTH: 500 VAC.
 LIFE EXPECTANCY: 1000 CYCLES MIN.

MECHANICAL:
 ACTUATION FORCE: 800g MAX.

ENVIRONMENTAL:
 OPERATING TEMPERATURE: -22°F TO +185°F (-30°C TO +85°C).
 STORAGE TEMPERATURE: -49°F TO +212°F (-45°C TO +100°C).

△ NOTES:

1. INTERPRET DRAWING PER ASME Y14.5M-1994.

MODEL#	DIM "L"	DIM "H"
SSV10	1.098	1.000
SSV08	.898	.800
SSV06	.698	.600
SSV04	.498	.400
SSV02	.298	.200

△ OUTLINE DRAWING
 SPECIFICATIONS ARE SUBJECT TO CHANGES WITHOUT NOTICE

THIS IS A C.A.D. GENERATED DRAWING.
 DO NOT MAKE MANUAL REVISIONS TO MASTER.

REV	REVISIONS
A	INITIAL RELEASE ESR# D244 P.S. APP'D: P.B. 7-9-87
B	REVISED ECOM# 2923 P.S. 6-2-88 APP'D: P.B.
3	REVISED ECOM# 1141-93 SEK 1-10-94 APP'D: J. SYLVIA 1-10-94
4	REVISED ECOM# 392-95 L.S. 6-6-95 APP'D: [Signature]

THIRD ANGLE PROJECTION

TOLERANCES (EXCEPT AS NOTED)
 ANGULAR = ±1°
 DECIMAL .XX = ±
 DECIMAL .XXX = ±.010
 DECIMAL .XXXX = ±

AUGAT CONFIDENTIAL
 This document contains information which is the exclusive property of Augat Inc.
 Distribution, reproduction or use by others is not permitted without the expressed written consent of Augat Inc.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES DO NOT SCALE PRINT	ORIGINAL DATE OF DRAWING: 6-87
FILE NAME: 80769OUT	DIRECTORY: SIPSWTCH
MATERIAL: SEE SPECIFICATIONS	FINISH: SEE SPECIFICATIONS
DRAWN: J.B.	DATE: 6-87
CHECKED: P.S.	DATE: 7-87
APPROVED: P.B.	DATE: 7-87
CODE IDENT. NO. 91506	DWG. SIZE C
NEXT ASSY:	

AUGAT INC. 452 JOHN DIETSCH BLVD. ATTLEBORO FALLS, MASS. 02763

TITLE: **OUTLINE DRAWING**
 SIP SWITCH
 (SSV02 - 10 SERIES)

DWG. NO. 80769

REV. 4

PRODUCT CODE: 022

SCALE: SHEET 1 OF 1

4 3 2 1