



- NOTES: UNLESS OTHERWISE SPECIFIED
1. MATERIAL: MOLDED PHENOLIC RESIN.
  2. EACH SET SCREW IS THREADED INTO A HIGH TORQUE, BRASS INSERT DESIGNED TO PREVENT THREAD STRIPPING.
  3. DECORATIVE SPUN ALUMINUM INLAY.
  4. COLOR: BLACK.
  5. THE PKD-10 SERIES IS THE SAME AS THE PKD SERIES EXCEPT THE ALUMINUM DIAL SKIRT HAS 0-10 GRADUATIONS SPACED 30° APART IN A COUNTER CLOCKWISE DIRECTION. NUMERALS ARE BLACK.
  6. INTERPRET DRAWING PER ASME Y14.5M-1994.

TYCO P/N	MODEL	SHAFT	"A"	"B"	"C"	"D"	"E"	"F"	"G"	"H"
2-1437624-7	PKD60B1/4	.250	.780	.566	.461	.487	.059	.217	.467	.563
2-1437624-8	PKD60B1/8	.125	.780	.566	.461	.487	.059	.217	.492	.563
2-1437624-9	PKD60B101/4	.250	.780	.566	.461	.487	.059	.217	.467	.563
3-1437624-0	PKD60B101/8	.125	.780	.566	.461	.487	.059	.217	.492	.563
3-1437624-1	PKD70B1/4	.250	1.050	.750	.645	.700	.080	.255	.490	.610
3-1437624-2	PKD70B101/4	.250	1.050	.750	.645	.700	.080	.255	.490	.610
2-1437624-5	PKD100B1/4	.250	1.310	.945	.804	.865	.047	.285	.512	.650
2-1437624-6	PKD100B101/4	.250	1.310	.945	.804	.865	.047	.285	.512	.650

3

	DIMENSION	TOLERANCE
SHAFT	.125 DIA	+.003 -0
	.250 DIA	+.003 -0

WAS DWG 80440

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN	15JUL04	Tyco Electronics Corporation Harrisburg, Pa 17105-3808	
DIMENSIONS: INCHES		BSV	-	Tyco Electronics	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK	-	NAME	
0. PLC	± -	APVD	-	PRODUCT SPEC	
1. PLC	± -	-		APPLICATION SPEC	
2. PLC	± -	-		RESTRICTED TO	
3. PLC	± .015	-		SIZE	
4. PLC	± -	-		CAGE CODE	
ANGLES	± -	-		DRAWING NO	
FINISH	-	-		WEIGHT	
SEE NOTE	-	-		A1 00779	
CUSTOMER DRAWING		SCALE 2.5:1		SHEET 1 OF 1	