


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
				NEW RELEASE	-	-	-



NOTES:

- CABLE ASSEMBLY TO BE 100% TESTED FOR OPENS, SHORTS & CONTINUITY
 HI-POT:200 VAC FOR 100ms
 INSULATION RESISTANCE: 50M OHMS MIN
 CONTINUITY RESISTANCE: 2 OHMS MAX
 FREQUENCY RANGE: DC TO 6 GHz
 VSWR: 1.5:1 MAX

1. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TYCO ELECTRONICS STANDARD 230-702.

8-1569301-4	2	31	2015381-1
PURCHASE CONTROL PART NO	TOLERANCE "T"	LENGTH "A"(mm)	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Dai guang hong 12Mar08	Tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608													
DIMENSIONS: mm [INCHES]		CHK Michael Han 12Mar08	NAME RF C/A, UMCC TO UMCC, TYPE I, 0.81MM CABLE													
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD Lessie Zhang 12Mar08	PRODUCT SPEC -													
<table border="1"> <tr><td>0 PLC</td><td>± -</td></tr> <tr><td>1 PLC</td><td>± -</td></tr> <tr><td>2 PLC</td><td>± -</td></tr> <tr><td>3 PLC</td><td>± -</td></tr> <tr><td>4 PLC</td><td>± -</td></tr> <tr><td>ANGLES</td><td>±</td></tr> </table>		0 PLC	± -	1 PLC	± -	2 PLC	± -	3 PLC	± -	4 PLC	± -	ANGLES	±	APPLICATION SPEC -		SIZE A3
0 PLC	± -															
1 PLC	± -															
2 PLC	± -															
3 PLC	± -															
4 PLC	± -															
ANGLES	±															
MATERIAL -	FINISH -	WEIGHT -	CAGE CODE 00779	DRAWING NO G-2015381												
CUSTOMER DRAWING			RESTRICTED TO -	SCALE N.T.S.												
			SHEET 1 OF 1	REV B												