

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT copyright\_daBe - ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
D		REVISED(ECR-14-016184)	11/18/14	DH	JK
E		REVISED(ECR-14-017721)	11/26/14	SH	HG
F		REVISED(ECR-16-004910)	11/APR/16	SH	KT
G		REVISED(ECR-17-001871)	09/FEB/17	SH	KT
H		REVISED(ECR-19-015398)	16/MAR/20	BH	YJ






TABLE 2.

3D VIEW  
SCALE 1:1

ASS'Y P/NO	0-2005575-1	1-2005575-2	3-2005575-3	4-2005575-8
DIM'				
COLOR	WHITE	BLACK	GRAY	BLUE



SECTION A-A






TABLE 1.

TYPE	FINISH	P/NO	WIRE RANG(mm <sup>2</sup> )
.060	PRE-TIN	2109006-1	0.22~0.35
		2109006-2	0.5~0.75
		2109006-3	0.85~1.25
.110	PRE-TIN	1743162-1	0.3~0.85
		1743163-1	1.25~2.0
.250	1) PRE-TIN	1743465-1	3.0
		1241402-1,3	0.5~1.0
		1241404-1,3	>1.0~2.5
		1241406-1,3	>2.5~4.0
		1241408-1,3	4.0~5.0

NOTE:  
 1. GENERAL TOLERANCE IS ±0.3, ±3'  
 Δ CONDITION OF DELIVERY;  
 DBL IN 1st LOCKING POSITION  
 LEVER IN 2nd LOCKING POSITION  
 Δ APPLICABLE RECEPTACLE CONTACT P/N;  
 TABLE 1.  
 Δ KEY CODE : SEE TABLE 2.

1) Selective silver plated  
 XXX-1 Pre-Tin Plated, XXX-3 Selective silver plated.





ASSY P/N	4-2005575-8	3-2005575-3	1-2005575-2	0-2005575-1	P/NAME
LIF 38P PLUG ASSY	LIF 38P PLUG ASSY	LIF 38P PLUG ASSY	LIF 38P PLUG ASSY	LIF 38P PLUG ASSY	

NO	NAME	COLOR	MATERIAL	Q'TY
3	LEVER	GRAY	PDM	1 - 1 1
		BLACK	PDM	- 1 - -
2	DBL	WHITE	PBT	2 2 2 2
		BLUE	PBT	1 - - -
1	PLUG HOUSING	GRAY	PBT	- 1 - -
		BLACK	PBT	- - 1 -
		WHITE	PBT	- - - 1


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SH JANG	-	
DIMENSIONS: mm		CHK KT JUNG	-	
TOLERANCES UNLESS OTHERWISE SPECIFIED		APVD KT LIM	-	
0 PLC ±		PRODUCT SPEC	-	
1 PLC SEE NOTE		APPLICATION SPEC	-	
2 PLC ±		WEIGHT	-	
3 PLC ±		SIZE A2	CAGE CODE 00779	DRAWING NO C=2005575
4 PLC ±		CUSTOMER DRAWING	SCALE 2:1	SHEET 1 OF 2
ANGLES ±		RESTRICTED TO -		
FINISH		REV H		

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT copyright\_da8e - ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			
		SEE SHEET 1 OF 2			



3D VIEW  
SCALE 1:1



SECTION A-A





TABLE 1.

TYPE	FINISH	P/NO	WIRE RANG(mm <sup>2</sup> )
.060	PRE-TIN	2109006-1	0.22~0.35
		2109006-2	0.5~0.75
		2109006-3	0.85~1.25
.110	PRE-TIN	1743162-1	0.3~0.85
		1743163-1	1.25~2.0
		1743465-1	3.0
250	1) PRE-TIN	1241402-1,3	0.5~1.0
		1241404-1,3	>1.0~2.5
		1241406-1,3	>2.5~4.0
		1241408-1,3	4.0~5.0

1) Selective silver plated  
 XXX-1 Pre-Tin Plated, XXX-3 Selective silver plated.

NOTE:  
 1. GENERAL TOLERANCE IS ±0.3, ±3'  
 △ CONDITION OF DELIVERY;  
 DBL IN 1st LOCKING POSITION  
 LEVER IN 2nd LOCKING POSITION  
 △ APPLICABLE RECEPTACLE CONTACT P/N;  
 TABLE 1.  
 △ MEANING OF (L) IS LONG LEVER.



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED	DWN	-
	0 PLC	CHK	-
	1 PLC	APVD	-
	2 PLC	PRODUCT SPEC	-
	3 PLC	APPLICATION SPEC	-
MATERIAL	FINISH	WEIGHT	-

TE Connectivity  
**LIF 38P(060/110/250) PLUG ASSEMBLY**

SIZE: A2 CAGE CODE: 00779 DRAWING NO: C=2005575 RESTRICTED TO: -  
 CUSTOMER DRAWING SCALE: 2:1 SHEET 2 OF 2 REV H

5-2005575-1 LIF 38P PLUG ASSY(L)  
 ASSY P/N P/NAME