





LOC		DIST		REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN	APVD	MS	CZ	YW
GP	00							
	A	RELEASED PER ECO-10-014866	21JUL2010	RG				
	A1	OBSOLETE	27AUG2024	CZ				



ISOMETRIC FRONT VIEW



CONNECTOR ACCEPTS
1.37-1.78
PCB



SECTION Z-Z

1 MATERIAL:
HOUSING - THERMOPLASTIC, GLASS REINFORCED,
COLOR: BLACK, UL94V-0 FLAMMABILITY RATED.
CONTACT - HIGH CONDUCTIVITY COPPER,

2 FINISH:
CONTACT - GOLD PLATE 0.76µm MIN. THK., OVER NICKEL
1.27µm MIN. THK
SOLDER TAILS - MATTE TIN 2.54µm MIN. THK.
OVER NICKEL 1.27µm MIN THK.

3. NO BURRS AND/OR SHARP EDGES ARE PERMISSABLE.

4 CONNECTOR ASSEMBLY MARKED WITH PART NUMBER
AND DATE CODE IN THIS AREA, APPROX. AS SHOWN.

5 DATUMS AND BASIC DIMENSIONS TO BE ESTABLISHED BY CUSTOMER.

3P X 8S	2057372-1
DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE WITHOUT NOTICE AND THE CONTROLLING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN D. LORD 31JUL2008	Tyco Electronics Harrisburg, PA 17105-3608	
DIMENSIONS: mm		CHK G. PETERS 15SEP2008	NAME CONNECTOR ASSY, STANDARD EDGE II RIGHT ANGLE 9 POWER X 8 SIGNAL	
		APVD A. FRANTUM 19SEP2008		
		PRODUCT SPEC		
		APPLICATION SPEC		
MATERIAL		108-2022	SIZE	RESTRICTED TO
		114-13018	CAGE CODE	DRAWING NO
		FINISH	2057372	REV
CUSTOMER DRAWING		WEIGHT	SCALE	SHEET
			6:1	1 OF 2



THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO THE CONTROL POLICY OF TYCO ELECTRONICS CORPORATION IT SHOULD BE CONTROLLED BY THE LATEST REVISION.		DWN D L ORD 31 JUL 2008		Tyco Electronics Harrisburg, PA 17105-3608	
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
mm		G. PETERS		CONNECTOR ASSY, STANDARD EDGE 11 RIGHT ANGLE 9 POWER X 8 SIGNAL	
		A FRANTUM		APVD	
1 P/LC ±		PRODUCT SPEC		SIZE	
1 P/LC ±		108-2022		CASE CODE	
2 P/LC ±0.25		APPLICATION SPEC		DRAWING NO	
3 P/LC ±		114-13018		RESTRICTED TO	
4 P/LC ANGLES ±3°		WEIGHT		A 00779 ©=2057372	
FINISH		-		SCALE 1:1	
MATERIAL		CUSTOMER DRAWING		SHEET 2 OF 2	
				REV A	